

**Rittal – The System.**

Faster – better – everywhere.



**SZ 2411.671**

**Cable gland, polyamide**

State: 11.05.2026. (Source: [rittal.com/hr-hr](https://www.rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2411.671 - Cable gland, polyamide

Integrated clamping membranes ensure reliable tightening and strain relief to protect the cables.

## Features

Model No.	SZ 2411.671
Benefits	Because the gland and lock nut are sold together in a single pack, this saves additional ordering and storage. Clamping membranes for even tightening and strain relief to protect the cables
Material	Polyamide 6 Seal: CR/NBR
Colour	RAL 7035
IP protection category to IEC 60529	IP 68 (5 bar, 30 min)
Dimensions	Height: 53 mm
Thread	M63 x 1.5
Thread length	18 mm
Min. cable diameter	34 mm
Max. cable diameter	44 mm
Operating temperature range	-30 °C...100 °C
torque	25 Nm
Width across flats	65 mm
Dimensions	Thread: M63 x 1.5 Thread length: 18 mm
Type rating to UL 50E	Type 1 Type 4 Type 4X Type 12 Type 13
Packs of	3 pc(s).

## Features

---

Net weight	0,372 kg
Gross weight	0,375 kg
Customs tariff number	39269097
ETIM 9	EC000441
ETIM 8	EC000441
ECLASS 8.0	27149109
Product description	SZ Cable gland, polyamide, size: M63x1,5, for cables ø 34-44 mm

---

## Approvals

---

Approvals	CSA + CSAus UL + C-UL (listed) VDE
Explanations	Declaration of conformity Declaration of conformity UK

---