Rittal – The System.

Faster - better - everywhere.





SK 3239.824 Blue e+ filter fan

State: 29.10.2025. (Source: rittal.com/hr-hr)



SK 3239.824 - Blue e+ filter fan EMC

Complete fan unit with EMC shielding for tool-free mounting on surfaces. Air throughput from 20 – $900 \, \text{m}^3\text{/h}$







Features

Model No.	SK 3239.824
Design	wall-mounted EMC
Product description	EMC fan-and-filter units offer a high shielding/attenuation effect and meet requirement category 2 to EN 61587-3.
Benefits	Easy filter changes, thanks to a new opening mechanism on the louvred grille Faster installation on the enclosure with optimised detent hooks Diagonal fan technology achieves more even and constant ventilation of the enclosure, thanks to improved pressure stability Tool-free assembly
Material	Plastic
Colour	RAL 7035
Supply includes	Complete unit ready to install, including EMC filter mat
Fan	Axial, DC motor
Air throughput, unimpeded airflow (with chopped-fibre filter)	With DC: 100 m³/h

© Rittal 2025

Features

Air throughput with matching outlet filter including chopped-fibre filter	With DC: 75 m³/h	
Rated operating voltage	24 V (DC)	
Power consumption Pel	With DC: 5.7 kW	
Rated current max.	With DC: 0.27 A	
Dimensions	Width: 204 mm Height: 204 mm Depth: 105 mm	
Installation depth	84 mm	
Mounting cut-out	Cut-out width: 177 mm Cut-out height: 177 mm	
IP protection category to IEC 60 529	IP 54 with chopped-fibre filter IP 56 with chopped-fibre filter and hose-proof hood	
Protection category NEMA	Type 12 with chopped-fibre filter Type 3, 3R, 4, 4X with chopped-fibre filter and hose-proof hood	
Pre-fuse	Miniature circuit-breaker/fuse: 2 A	
Note	To improve energy efficiency and extend the service life of the devices, we recommend the use of thermostats or temperature displays	
Operating temperature range	-15 °C55 °C	
Storage temperature range	-30 °C70 °C	
Noise level	With DC: 51 dB(A)	
Packs of	1 pc(s).	
Net weight	1.1	
Gross weight	1.24	
Customs tariff number	84145915	
EAN	4028177985537	
ETIM 9	EC000320	
ETIM 8	EC000320	

© Rittal 2025 3

Features

S 8.0 27180716

Approvals

Approvals	30 - KC Korea
	UL + C-UL - FTTA
	UR + C-UR (recognized)
Explanations	Declaration of conformity

© Rittal 2025