


Rittal – The System.

Faster – better – everywhere.



SK 3238.724 Blue e+ filter fan

State: 16.09.2025. (Source: [rittal.com/hr-hr](https://www.rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3238.724 - Blue e+ filter fan

Complete fan-and-filter units for tool-free installation in surfaces. Air throughput 20 – 1,160 m³/h, protection category IP 54 as standard.



Features

| | |
|---------------------|---|
| Model No. | SK 3238.724 |
| Design | wall-mounted |
| Product description | Fan-and-filter units with diagonal fan technology have superior pressure stability and ensure a more constant air throughput. The diagonal direction of outflow ensures more even heat dissipation from the enclosure. |
| Benefits | <p>Maximum air throughput via pleated filter included in the delivered state</p> <p>Easy filter changes, thanks to a new opening mechanism on the louvred grille</p> <p>Faster installation on the enclosure with optimised detent hooks</p> <p>Diagonal fan technology achieves more even and constant ventilation of the enclosure, thanks to improved pressure stability</p> <p>Tool-free assembly</p> |
| Material | Plastic |
| Colour | RAL 7035 |
| Supply includes | Complete unit ready to install, including pleated filter |
| Fan | Axial, DC motor |

Features

| | |
|---|--|
| Air throughput, unimpeded airflow (with chopped-fibre filter) | With DC: 53 m³/h |
| Air throughput, unimpeded airflow (with pleated filter) | With DC: 63 m³/h |
| Air throughput with matching outlet filter including chopped-fibre filter | With DC: 40 m³/h |
| Air throughput with matching outlet filter including pleated filter | With DC: 49 m³/h |
| Rated operating voltage | 24 V (DC) |
| Power consumption Pel | With DC: 5.7 W |
| Rated current max. | With DC: 0.27 A |
| Dimensions | Width: 148.5 mm Height: 148.5 mm Depth: 82.5 mm |
| Installation depth | 64 mm |
| Mounting cut-out | Cut-out width: 124 mm Cut-out height: 124 mm |
| IP protection category to IEC 60 529 | IP 54 with chopped-fibre filter/pleated filter IP 55 with pleated filter and absorber mat IP 56 with chopped-fibre filter/pleated filter and hose-proof hood |
| Protection category NEMA | Type 12 with chopped-fibre filter/pleated filter Type 3, 3R, 4, 4X with chopped-fibre filter/pleated filter and hose- proof hood |
| Pre-fuse | Miniature circuit-breaker/fuse: 2 A |
| Note | With the filter fan 3237.XXX, electrical connection is made via two single wires (length approx. 300 mm) on the unit, for all other filter fans, a screwless spring terminal is used |
| Operating temperature range | -15 °C...55 °C |
| Storage temperature range | -30 °C...70 °C |
| Noise level | With DC: 52 dB(A) |
| Packs of | 1 pc(s). |

Features

| | |
|-----------------------|---------------|
| Net weight | 0.45 |
| Gross weight | 0.607 |
| Customs tariff number | 84145915 |
| EAN | 4028177998223 |
| ETIM 9 | EC000320 |
| ETIM 8 | EC000320 |
| ECLASS 8.0 | 27180716 |

Approvals

| | |
|--------------|---|
| Approvals | 30 - KC Korea UL + C-UL - FTTA UR + C-UR (recognized) |
| Explanations | Declaration of conformity |