## Rittal – The System.

Faster – better – everywhere.





# SK 3244.710 Blue e+ filter fan

State: 14.12.2025. (Source: rittal.com/hr-hr)



#### SK 3244.710 - Blue e+ filter fan

Complete fan-and-filter units for tool-free installation in surfaces. Air throughput  $20-1,160~\text{m}^3/\text{h}$ , protection category IP 54 as standard.







#### **Features**

Model No.	SK 3244.710
Design	wall-mounted
Product description	Fan-and-filter units with diagonal fan technology have superior pressure stability and ensure a more constant air throughput. The diagonal direction of outflow ensures more even heat dissipation from the enclosure.
Benefits	Maximum air throughput via pleated filter included in the delivered state  Easy filter changes, thanks to a new opening mechanism on the louvred grille  Faster installation on the enclosure with optimised detent hooks  Diagonal fan technology achieves more even and constant ventilation of the enclosure, thanks to improved pressure stability  Tool-free assembly
Material	Plastic
Colour	RAL 7035
Supply includes	Complete unit ready to install, including pleated filter
Fan	Diagonal, 1~ capacitor motor

© Rittal 2025

## Features

Air throughput, unimpeded airflow	At 50 Hz: 700 m³/h
(with chopped-fibre filter)	At 60 Hz: 770 m³/h
Air throughput, unimpeded airflow	At 50 Hz: 867 m³/h
(with pleated filter)	At 60 Hz: 910 m³/h
Air throughput with matching	At 50 Hz: 537 m³/h
outlet filter including chopped-fibre filter	At 60 Hz: 587 m³/h
Air throughput with matching	At 50 Hz: 720 m³/h
outlet filter including pleated filter	At 60 Hz: 745 m³/h
Rated operating voltage	115 V, 1~, 50 Hz/60 Hz
Power consumption Pel	At 50 Hz: 120.7 W
	At 60 Hz: 166.1 W
Rated current max.	At 50 Hz: 1.06 A
	At 60 Hz: 1.47 A
Dimensions	Width: 323 mm
	Height: 323 mm
	Depth: 156 mm
Installation depth	136 mm
Mounting cut-out	Cut-out width: 292 mm
-	Cut-out height: 292 mm
IP protection category to IEC 60	IP 54 with chopped-fibre filter/pleated filter
529	IP 55 with pleated filter and absorber mat
	IP 56 with chopped-fibre filter/pleated filter and hose-proof hood
Protection category NEMA	Type 12 with chopped-fibre filter/pleated filter
	Type 3, 3R, 4, 4X with chopped-fibre filter/pleated filter and hose-
	proof hood
Pre-fuse	Miniature circuit-breaker/fuse: 6 A
Note	With the filter fan 3237.XXX, electrical connection is made via two
	single wires (length approx. 300 mm) on the unit, for all other filter
	fans, a screwless spring terminal is used
Operating temperature range	-30 °C55 °C
Storage temperature range	-30 °C70 °C

© Rittal 2025 3

## Features

Noise level	At 50 Hz: 64 dB(A)
	At 60 Hz: 66 dB(A)
Packs of	1 pc(s).
Net weight	4.9
Gross weight	5.011
Customs tariff number	84145915
EAN	4028177997899
ETIM 9	EC000320
ETIM 8	EC000320
ECLASS 8.0	27180716

# Approvals

Approvals	CSA
	30 - KC Korea
	UL + C-UL - FTTA
	UR + C-UR (recognized)
Explanations	Declaration of conformity

© Rittal 2025