

# Rittal – The System.

Faster – better – everywhere.



## SK 3366.545

# TopTherm wall-mounted cooling unit Blue e

State: 21.05.2026. (Source: [rittal.com/hr-hr](http://rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3366.545 - TopTherm wall-mounted cooling unit Blue e 0.3 - 4 kW

Energy-efficient Blue e wall-mounted cooling units in the output categories 300 W to 4000 W and with integral electrical condensate evaporator (from 1000 W). Available in the special formats "horizontal" and "flat".



## Features

|                     |   |
|---------------------|---|
| Model No.           | SK 3366.545   |
| Design              | wall-mounted<br>Flat  |
| Product description | Energy-efficient Blue e wall-mounted cooling units in the output categories 300 W to 4000 W and with integral electrical condensate evaporator (from 1000 W).   |
| Benefits            | May be linked to the IoT interface via Blue e IoT adaptor for cooling units from 500 W cooling output with e-Comfort controller   |
| Material            | Sheet steel   |
| Colour              | RAL 7035  |
| Supply includes     | Fully wired ready for connection (plug-in terminal strip)<br>Drilling template<br>Assembly parts<br>Integral electric condensate evaporation<br>Assembly parts for internal mounting<br>Condenser with hydrophobic RiNano coating |

# Features

|  |   |
|--|---|
| Total cooling output to DIN EN 14511           | Cooling output L35 L35/50 Hz: 1.25 kW<br>Cooling output L35 L35/60 Hz: 1.25 kW<br>Cooling output L35 L50/50 Hz: 0.8 kW<br>Cooling output L35 L50/60 Hz: 0.92 kW |
| Rated operating voltage                        | 400 V, 3~, 50 Hz<br>460 V, 3~, 60 Hz  |
| Note on Model No.                              | For external mounting of the cooling unit, trim frame 3377.000 including assembly parts may be fitted. This gives the cooling unit a closed front appearance.   |
| Rated current max.                             | At 50 Hz: 1.9 A<br>At 60 Hz: 1.8 A  |
| Start-up current max.                          | At 50 Hz: 6 A<br>At 60 Hz: 6 A  |
| Air throughput (unimpeded air flow)            | External circuit: 910 m <sup>3</sup> /h<br>Internal circuit: 860 m <sup>3</sup> /h  |
| Energy efficiency ratio (EER) 50/60 Hz L35 L35 | Refrigeration factor L35 L35 (EER) 50 Hz: 1.56<br>Refrigeration factor L35 L35 (EER) 60 Hz: 1.39  |
| Design   | wall-mounted  |
| Special design                                 | Flat  |
| Dimensions                                     | Width: 435 mm<br>Height: 1,590 mm<br>Depth: 205 mm  |
| Protection category to IEC 60 529              | External circuit IP 34<br>Internal circuit IP 54  |
| Protection category NEMA                       | UL Type 12  |
| Refrigerant/cooling medium                     | Refrigerant: R-513A<br>Quantity: 0.7 kg<br>Global Warming Potential (GWP): 631<br>CO <sub>2</sub> equivalent (CO <sub>2</sub> e): 0.44 t                        |
| Temperature control                            | e-Comfort controller (factory setting +35 °C)   |
| Operating temperature range                    | 10 °C...55 °C   |
| Storage temperature range                      | -40 °C...70 °C  |

# Features

---

|  |   |
|--|---|
| Setting range                            | 20 °C...50 °C   |
| Power consumption Pel                    | Power consumption L35 L35/50 Hz: 0.7 kW<br>Power consumption L35 L35/60 Hz: 0.8 kW<br>Power consumption L35 L50/50 Hz: 0.8 kW<br>Power consumption L35 L50/60 Hz: 0.92 kW |
| Permissible operating pressure (p. max.) | 28 bar  |
| Pre-fuse                                 | Transformer circuit-breaker: 2 A  |
| Packs of                                 | 1 pc(s).  |
| Net weight                               | 50 kg   |
| Gross weight                             | 58,5 kg   |
| Customs tariff number                    | 84158200  |
| ETIM 9                                   | EC000855  |
| ETIM 8                                   | EC000855  |
| ECLASS 8.0                               | 27180704  |
| Product description                      | SK Cooling unit Blue e, wall-mounted, slimline, 1.25 kW, 400-460 V, 3~, 50-60 Hz, sheet steel, WHD: 435 x 1590 x 205 mm   |

# Approvals

---

|              |   |
|--------------|---|
| Explanations | Declaration of conformity<br>Declaration of conformity - F-gas regulation |
|--------------|---|