

Rittal – The System.

Faster – better – everywhere.



SK 3318.600 TopTherm chillers

State: 01.06.2025. (Source: rittal.com/hr-hr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3318.600 - TopTherm chillers 1,3 - 7 kW

Roof-mounted and stand-alone TopTherm chillers are both flexible and compact. They provide for economical chilling of a central cooling water supply for air/water heat exchangers or the like. With nano-coated condenser as standard.

Features

Model No.	SK 3318.600
Design	Compact, modular layout of the refrigeration components Pump to convey the medium
Benefits	Precise temperature control, based on microprocessor technology Collective fault signal with floating contact One version for two frequencies = international compatibility
Colour	RAL 7035
Supply includes	Condenser with hydrophobic RiNano coating Complete unit ready for connection Multilingual documentation including functional diagram and wiring plans
Protection category to IEC 60 529	IP 44 (electrics)
Total cooling output Tw10 / Tu32	Cooling output Tw10 Tu32/50 Hz: 0.8 kW Cooling output Tw10 Tu32/60 Hz: 0.9 kW
Total cooling output Tw18 / Tu32	Cooling output Tw18 Tu32/50 Hz: 1 kW Cooling output Tw18 Tu32/60 Hz: 1.1 kW
Air throughput (unimpeded air flow)	At 50 Hz: 900 m³/h At 60 Hz: 900 m³/h
Rated operating voltage	230 V, 1~, 50 Hz/60 Hz
Dimensions	Width: 600 mm Height: 400 mm Depth: 430 mm
Temperature control	Microcontroller control (factory setting +20 °C)
Operating temperature range	10 °C...43 °C

Features

Operating temperature range of cooling medium	10 °C...30 °C
Temperature hysteresis	± 2 K
Refrigerant/cooling medium	Refrigerant: R134a Quantity: 0.975 kg Global Warming Potential (GWP): 1,430 CO2 equivalent (CO2e): 1.39 t
Power consumption Pel	At 50 Hz: 0.69 kW At 60 Hz: 1.07 kW
Rated current max.	At 50 Hz: 5.1 A At 60 Hz: 5.6 A
Water circuit	Pressure-sealed
Water connections	G ½" internal thread
Number of cooling circuits	1
Packs of	1 pc(s).
Net weight	47
Gross weight	48
Customs tariff number	84186900
EAN	4028177351134
ETIM 9	EC002516
ETIM 8	EC002516
ECLASS 8.0	27180713

Approvals

Explanations	Declaration of conformity
--------------	---------------------------

Tender text

Chiller TopTherm

Benefits: Precise temperature control, based on microprocessor technology, Collective fault signal with floating contact, One version for two frequencies = international compatibility

Design: Compact, modular layout of the refrigeration components, hydrophobic RiNano-coated condenser, Pump to convey the medium

Total cooling output TW10 TU32, 50/60 Hz: 0,8 / 0,9 kW

Total cooling output TW18 TU32, 50/60 Hz: 1 / 1,1 kW

Power consumption 50/60 Hz: 0,69 / 1,07 kW

Rated power input 50/60 Hz: 5,1 / 5,6 A

Rated operating voltage: 230 V, 1~, 50/60 Hz

Temperature control: Microcontroller control (factory setting +20 °C)

Dimensions [WxHxD]: 600x400x430 mm

Colour: RAL 7035

Refrigerant / Quantity: R134a / 975 g

Water circuit: Pressure-sealed

Water connections: G 1/2" IG

Operating temperature range: 10 °C to 43 °C

Liquid media temperature range: 10 °C to 30 °C

Temperature hysteresis: +/- 2 K

Number of cooling circuits: 1

Protection category IP to IEC 60 529: IP 44 (electronics)

Weight: 48 kg