### Rittal – The System.

Faster – better – everywhere.





## AS 4055.140 Splitter hole punch, round

State: 18.11.2025. (Source: rittal.com/hr-hr)



# AS 4055.140 - Splitter hole punch, round for stainless steel, round, with triple splitting

For punching round cut-outs

#### **Features**

Model No.	AS 4055.140	
Design	With triple splitting	
Product description	For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch.	
Supply includes	Female dies Male dies	
Machinable material	Stainless steel	
Maximum machinable material thickness, stainless steel	2,5 mm	
Ø punch	40,5 mm	
For threads	M40	
Note	When operating with wrenches, tension screws with ball bearings should be used.	
Suitable for hydraulic bolt order number	4055.663	
Tension screw (Ø x L)	19 x 75 mm	
Hydraulic tension screw Ø	19 mm	
Packs of	1 pc(s).	
Net weight	0.386	
Gross weight	0.417	
Customs tariff number	82073010	
EAN	4028177808089	
ETIM 9	EC000156	

© Rittal 2025

### **Features**

ETIM 8	EC000156	
ECLASS 8.0	21049047	

© Rittal 2025 3