

Rittal – The System.

Faster – better – everywhere.



SV 3418.010

Bus-mounting fuse base

State: 22.05.2026. (Source: rittal.com/hr-hr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 3418.010 - Bus-mounting fuse base

3-pole, for 60 mm bar centre distance.

Features

Model No.	SV 3418.010
Material	Bus-mounting fuse base: Fibreglass-reinforced, thermoplastic polyester (PBT) Contact hazard protection: Polyamide Fire protection corresponding to UL 94-V0
Colour	RAL 7035
Note	Wire end ferrules should be used with fine wire conductors
For bar systems with centre-to-centre spacing	60 mm
Type of electrical connection	Box terminal
Fuse inserts	D 02-E 18 (adaptor sleeve)
Rated insulation voltage U_i	690 V
Rated current max.	63 A
Rated operating voltage	400 V, 3~
Note	For the use of fuse inserts to EN 60 269-3 (DIN VDE 0636-3)
Dimensions	Width: 27 mm Height: 209 mm
Connection of round conductors	1.5 - 25 mm ²
To fit busbars	Height: 5, 10 mm
Number of poles	3-pole
Rated operating voltage (L1 + L2)	400 V (DC)
Rated operating voltage (L1 + L3)	400 V (DC)
Round conductor cross-section	1.5 - 25 mm ²
Packs of	10 pc(s).

Features

Net weight	1,69 kg
Gross weight	1,78 kg
Copper weight (kg per piece)	0,018
Customs tariff number	85369095
ETIM 9	EC001644
ETIM 8	EC001644
ECLASS 8.0	27142120
Product description	SV Bus-mounting fuse base, D02-E18, 63 A, 400 V, 3-pole, round conductor connection 1,5-25 mm ² , adaptor sleeve

Approvals

Approvals	ABS DNV Lloyds Register
Explanations	Declaration of conformity