

Rittal – The System.

Faster – better – everywhere.



HD 4000.250 Levelling feet HD

State: 17.11.2025. (Source: rittal.com/hr-hr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



HD 4000.250 - Levelling feet HD

Levelling feet HD minimise cleaning time thanks to fully covered, permanently sealed threads and provide compensation of floor inclines up to an angle of 10° thanks to flexible base plate.

Features

| | |
|-----------------------|--|
| Model No. | HD 4000.250 |
| Design | with base attachment |
| Benefits | Minimises cleaning time thanks to fully covered, permanently sealed threads Compensation of floor inclines up to an angle of 10° thanks to flexible base Baying can even be achieved on sloping floors, thanks to a large levelling range Certification to 3-A Sanitary Standards |
| Material | Stainless steel 1.4301 (AISI 304) |
| Supply includes | Assembly parts and seals |
| Load capacity | Max. 7000 N static per levelling foot |
| Dimensions | Thread: M12 |
| To fit | Enclosure type: HD compact enclosure VX VX SE TS |
| Levelling range | 122 - 175 mm |
| Packs of | 4 pc(s). |
| Net weight | 2.4 |
| Gross weight | 2.5 |
| Customs tariff number | 73181900 |
| EAN | 4028177707658 |
| ETIM 9 | EC002622 |
| ETIM 8 | EC002622 |

Features

ECLASS 8.0

27189263