


Rittal – The System.

Faster – better – everywhere.



AS 4050.315

Laser centre Perforex LC 3030

State: 15.05.2024. (Source: [rittal.com/hr-hr](https://www.rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4050.315 - Laser centre Perforex LC 3030

Perforex laser centres are specifically designed for the automated mechanical modification of standard enclosures. The Perforex LC specialises in 3D laser machining of cubes and contactless, low-vibration machining. Machining of mounting plates including tapped holes is also supported.



Features

Model No.	AS 4050.315
Design	Perforex LC 3015
Product description	Perforex laser centres are specially designed for the automated mechanical modification of standard enclosures. The Perforex LC specialises in 3D laser machining of cubes and contactless, low-vibration machining. Machining of mounting plates including tapped holes is also supported.
Benefits	<ul style="list-style-type: none">3D enclosure machining without repositioning the workpieceNo tarnishing or discolouration of the cut edges when machining stainless steelSpray-finished metal parts, even those with delicate contours, can be cut without damaging the paint or causing discolourationProduct spectrum from compact to large enclosuresContactless, low-vibration machining with no tool wearNo need to clamp the workpiecesMachining speed with stainless steel 20x faster than with conventional milling processErgonomic working, thanks to the extendible support surface for enclosure and panel machiningSimultaneous machining of 5 sides
Technical specifications	<ul style="list-style-type: none">Laser pointer (auxiliary laser), beam power laser class 1Very narrow cutting width of just 0.3 mm (approx.)Class 4 laser

Features

Material	Stainless steel Sheet steel Sheet steel, powder-coated
Supply includes	Laser centre Compressor Machine housing Filter system Operating unit
Machinable material	Stainless steel Sheet steel Aluminium
Machine controller	Workshop programming
Safety	Protective housing to achieve laser class 1. May be operated by properly trained personnel, no need for a laser specialist Security door
Interfaces	EPLAN Pro Panel Transfer of DXF formats
Note	Safety roof (4050.317) for machine housing is mandatory if the machine can be viewed from above A site inspection by a Rittal specialist to select and define the laser version required is necessary We reserve the right to make technical modifications
Support area	Width: 3,900 mm Height: 3,800 mm Depth: 10,500 mm
Beam power max.	150 W (CW) or 1500 W (pulse)
Pulse energy (max.)	15 J
Duration of pulse, max.	50 µs at 150 W output
Wavelength	1.070 nm
Maximum machinable material thickness, sheet steel	3 mm
Maximum machinable material thickness, stainless steel	3 mm
Control voltage (DC)	24 V

Features

Power consumption	1,5 kW
Rated operating voltage	400 V, 3~, 50 Hz
Max. machinable area of cubes	Width: 1,270 mm Height: 2,250 mm Depth: 800 mm
Support area	Width: 3,900 mm Height: 3,800 mm Depth: 10,500 mm
Packs of	1 pc(s).
Customs tariff number	84561190
EAN	4028177804760
ETIM 7.0	EC000000
ECLASS 8.0	36620404