

# Rittal – The System.

Faster – better – everywhere.



## AS 4051.123

## Wire Station WS 540

State: 18.07.2025. (Source: [rittal.com/hr-hr](https://www.rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4051.123 - Wire Station WS 540

Mobile wiring workstation, height-adjustable, for flexible use in the workshop. For ergonomic, fatigue-free wire processing work.



## Features

Model No.	AS 4051.123
Design	US version
Product description	Mobile wiring workstation, height-adjustable, for flexible use in the workshop. For ergonomic, fatigue-free wire processing work.
Benefits	<p>Electronically adjustable desk for the optimum working height, adjustable from 710 – 1250 mm</p> <p>Multiplex worktop, washable and scratch-resistant</p> <p>Ideal solution in conjunction with the length-cutting and crimping machines plus pre-assembled wires with the Wire Terminal</p> <p>Integral scale for quick manual measurements</p> <p>Prepared to accommodate a monitor for wire processing with Eplan Smart Wiring</p> <p>Optionally expandable with shelves for wire boxes, wire reels and holders for tools and small parts</p> <p>For flexible use in the workshop thanks to rubberised wheels</p> <p>Drawer with shadow board prepared for tools</p>
Supply includes	<p>Wiring table with electrical height adjuster</p> <p>Connection cable, 7 m</p> <p>7-way socket strip, with rocker switch</p>
Assembly instruction	The vertical mounting struts, Model No. 4051.106, are required for accessories such as storage box holders, magazine supports etc.
Input voltage	110 V AC, 60 Hz

# Features

Dimensions	Width: 900 mm Height: 1,350 mm Depth: 781 mm
Working height	Working height (min.): 710 mm Working height (max.): 1,205 mm
Height adjustable y/n	Yes
Packs of	1 pc(s).
Net weight	95
Gross weight	106
Customs tariff number	94032080
EAN	4028177962668
ETIM 9	EC000348
ETIM 8	EC002224
ECLASS 8.0	21100208

# Approvals

Explanations	Declaration of conformity
--------------	---------------------------