## Rittal – The System.

Faster - better - everywhere.





# AS 4052.104 Screwdrivers

State: 16.11.2025. (Source: rittal.com/hr-hr)



### AS 4052.104 - Screwdrivers insulated

With a long, slender handle and high-performance tip with non-transfer insulation.

#### **Features**

| Model No.                 | AS 4052.104   |
|---------------------------|---|
| Design                    | Isolation protection 1000 V<br>for slot-head screws   |
| Product description       | With a long, slender handle and high-performance tip with non-transfer insulation.  |
| Benefits                  | Minimal force required, thanks to ergonomically styled handle Handle head with anti-roll protection and clear screw labelling Black coated blade tip to preserve precision and accuracy of fit Handle 30% and insulation up to 50% slimmer than comparable tools  Optimum interconnection of hand and handle supports higher torques and longer, fatigue-free working |
| Material                  | Blade: Chrome-molybdenum-vanadium alloy<br>Handle core: Hard plastic<br>Handle body: Elastic, highly flexible plastic   |
| Colour                    | Handle: Anthracite and Rittal Power Pink  |
| Blade dia.                | 4 mm  |
| Blade length              | 100 mm  |
| Blade (width x thickness) | 4 x 0.8 mm  |
| Blade tip                 | SL  |
| Handle dia.               | 25 mm   |
| Handle length             | 105 mm  |
| Standards                 | IEC 60 900  |
| Packs of                  | 3 pc(s).  |
| Net weight                | 0.135   |
| Customs tariff number     | 82054000  |

© Rittal 2025

#### **Features**

| EAN        | 4028177807228 |
|------------|---------------|
| ETIM 9     | EC000144      |
| ETIM 8     | EC000158      |
| ECLASS 8.0 | 21040406      |

© Rittal 2025 3