


Rittal – The System.

Faster – better – everywhere.



DK 5302.014 Air baffle plate

State: 14.07.2025. (Source: [rittal.com/hr-hr](https://www.rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5302.014 - Air baffle plate for VX IT 482.6 mm (19") mounting angles, standard

To separate the hot/cold zones within an enclosure with aisle containment or when using an LCP system.



Features

| | |
|-----------------|---|
| Model No. | DK 5302.014 |
| Benefits | To selectively boost the energy efficiency of your climate control system Vertical brush strip for collision-free shielding with installed rail systems on the outer mounting level. |
| Applications | To separate the hot/cold zones within an enclosure with aisle containment or when using an LCP system. |
| Material | Sheet steel Blanking panel: Plastic, UL 94-HB, halogen-free Brush strip: Plastic, UL 94-HB |
| Surface finish | Spray-finished |
| Colour | RAL 9005 |
| Supply includes | 2 vertical trim panels 2 horizontal trim panels 4 brush strips 4 cellular PU foam pieces Assembly parts 6 blanking panels, 482.6 mm (19"), 1 U |

Features

| | |
|-------------------------------|--|
| Assembly instruction | <p>The vertical trim panels with brush strip may be fitted on both the front and rear 482.6 mm (19") mounting angles for partitioning.</p> <p>The horizontal trim panels with brush strips can only be mounted on the front 482.6 mm (19") mounting angles.</p> <p>482.6 mm (19") mounting cut-outs integrated within the partitioning areas may optionally be sealed with the supplied blanking panels, or used to install additional components or for cable routing. Please see the product-specific scope of supply.</p> |
| To fit | <p>Width: = 800 mm</p> <p>Height: = 2,000 mm</p> |
| Packs of | 1 pc(s). |
| Net weight | 8.26 |
| Gross weight | 8.48 |
| PCF per pack (cradle-to-gate) | 33.1 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 73269098 |
| EAN | 4028177955295 |
| E-Number Sweden | E7282586 |
| ETIM 9 | EC000331 |
| ECLASS 8.0 | 27189272 |