


Rittal – The System.

Faster – better – everywhere.



DK 5501.615

Component shelf 2 U, static installation

State: 15.08.2025. (Source: [rittal.com/hr-hr](https://www.rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE



SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5501.615 - Component shelf 2 U, static installation

Component shelf 2 U, static installation for attachment to the 482.6 mm (19") system punchings.
Load capacity: 25 kg.



Features

| | |
|-------------------------------|--|
| Model No. | DK 5501.615 |
| Design | 482.6 mm (19") |
| Product description | For mounting between 482.6 mm (19") mounting angles. |
| Material | Sheet steel |
| Surface finish | Spray-finished |
| Colour | RAL 9005 |
| Load capacity | 25 kg surface load, static |
| Note | Not suitable for combination with telescopic slides. |
| Dimensions | Width: 482.6 mm Depth: 250 mm |
| Packs of | 1 pc(s). |
| Net weight | 2.078 |
| Gross weight | 2.125 |
| PCF per pack (cradle-to-gate) | 9.5 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |

Features

| | |
|-----------------------|---------------|
| Customs tariff number | 73269098 |
| EAN | 4028177679054 |
| E-Number Sweden | E7239584 |
| ETIM 9 | EC002620 |
| ECLASS 8.0 | 27189261 |