
Rittal – The System.

Faster - better - everywhere.





VX 5302.157

482.6 mm (19") mounting angles, dynamic

State: 05.11.2025. (Source: rittal.com/hr-hr)



VX 5302.157 - 482.6 mm (19") mounting angles, dynamic for VX IT

Mounting angles, also for accommodating server system installation kits.

Features

Suitable for assembling a 482.6 mm (19") mounting level or for 482.6 mm (19") partial installation. The L-shaped design can directly accommodate all commercially available mounting kits for server systems, which are fastened directly to the 482.6 mm (19") system punchings.
Integral, bidirectional U labelling Integral system punchings on a U pitch pattern on the front and sides, allows U-specific mounting of cable routing components for structured cabling
Side punchings, round and square, on a U pitch pattern Potential equalisation within the mounting level and with the locating frame is achieved via the assembly components 482.6 mm (19") mounting hole including U centre fixing attachment to standard EIA 310 E
For mounting a 482.6 mm (19") mounting level within the VX IT rack system
Sheet steel, 2.5 mm
Primed
RAL 9005
Assembly parts
rear
Alternative installation widths from 21" – 24", depending on the mounting variant and rack dimensions selected

© Rittal 2025

Features

Assembly instruction	To be combined with cross-member, depth stays or mounting bracket for attachment Use of the different mounting options depends on the relevant enclosure dimensions
To fit	Height: = 47 U
Packs of	2 pc(s).
Net weight	14.4
Gross weight	14.9
PCF per pack (cradle-to-gate)	56.8 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73269098
EAN	4028177960039
ETIM 9	EC002620
ECLASS 8.0	27189261

© Rittal 2025 3