

Rittal – The System.

Faster – better – everywhere.



DK 5509.161

Network/server enclosure TS IT

State: 21.07.2025. (Source: [rittal.com/hr-hr](https://www.rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5509.161 - Network/server enclosure TS IT with vented door, pre-configured, with 482.6 mm (19") mounting frame

TS IT, vented, for room climate control. Supplied pre-assembled with a selection of practical equipment. 482.6 mm (19") interior installation with 482.6 mm (19") mounting frame for a load capacity of up to 1,500 kg, available in a range of size variants.

Features

Model No.	DK 5509.161
Material	Sheet steel Aluminium Base/plinth corner piece: Sheet steel Base/plinth trim panel front/rear: Sheet steel Corner and baying cover: Plastic
Surface finish	Enclosure frame: Dipcoat-primed Interior installation: Dipcoat-primed Doors, roof and side panels: Dipcoat-primed and powder-coated
General colour	RAL 7035
Colour	Enclosure frame and panels: RAL 7035 Interior installation, vent grille at the front, base/plinth: RAL 9005

Features

Supply includes	<p>TS 8 enclosure frame with doors and roof plate</p> <p>Aluminium/sheet steel door at the front, vented (vented surface area approx. 85% perforated), 180° hinges</p> <p>Sheet steel rear door, vented (vented surface area approx. 85% perforated), vertically divided, 180° hinges</p> <p>Lock front and rear: Comfort handle for profile half-cylinders and security lock 3524 E</p> <p>Two 482.6 mm (19") mounting frames, front and rear, depth-variable</p> <p>Side panels, one-piece, lockable</p> <p>Roof plate, multi-piece, removable, with side cable entry in the depth and covered cut-out for fan mounting plate</p> <p>Base mount</p> <p>Gland plate, one-piece, vented, with cable entry at the rear</p> <p>Base/plinth system VX, 100 mm, vented</p> <p>Base/plinth corner pieces and trim panels, sides, screw-fastened</p> <p>Base/plinth trim panels, front and rear plus corner and baying covers supplied loose</p> <p>4 levelling feet, M12, including base/plinth adaptor (supplied loose)</p> <p>Spacers, height 50 mm, to raise a cover plate above the fan cut-out in the roof plate, for passive cooling (supplied loose). Not required for variants without a cut-out.</p> <p>12 x 482.6 mm (19") fastener, 1 U, conductive (supplied loose)</p> <p>50 multi-tooth screws, conductive (supplied loose)</p> <p>4 cable clamp rails (T-head) for outer mounting level, to fit enclosure depth (supplied loose)</p> <p>10 cable shunting rings, metal, 125 x 65 mm (supplied loose)</p> <p>Connection accessories for potential equalisation incl. central earthing point, pre-configured</p> <p>IPPC pallet</p>
Dimensions	<p>Width: 800 mm</p> <p>Height: 2,000 mm</p> <p>Depth: 1,000 mm</p>
Units	42 U
Units	42 U
Height including base/plinth	2.100 mm
Free mounting space to the 482.6 mm (19") level, front/rear	87 mm / 165 mm

Features

Distance between levels as delivered	745 mm
Design doors	Vented
482.6 mm (19") level(s) version	Mounting frame, 482.6 mm (19")
Load capacity	15.000 N
Note	Depending on how and where it is sited, the door opening angle may vary for selected applications
Basic material	Aluminium
Packs of	1 pc(s).
Net weight	155.5
Gross weight	161.5
EAN	4028177706071
E-Number Sweden	E7239910
ETIM 9	EC002499
ECLASS 8.0	27180207

Approvals

Approvals	UL + C-UL (listed)
Certificates	Surface finish
Explanations	Declaration of conformity

Tender text

TS IT 5509.161

TS IT network server enclosure for room climate control with vented doors, with 482.6 mm (19") mounting frame, base/plinth and side panels, pre-configured

Pre-configured IT rack for stand-alone siting with side panels and 100 mm VX base/plinth system vented at the front and rear.

Installation height 42 U, vented sheet steel door at the front, two-part solid sheet steel door at the rear.

Pre-configured IT rack consisting of torsionally stiff, welded symmetrical frame of rolled 16-fold vertical sections connected with two horizontal frames of rolled 9-fold sections with integral channel for accommodating the side panel seal and protecting it against possible effect of aggressive media.

All frame sections, with integral system punchings on a 25 mm DIN pitch pattern, allow convenient interior installation by simple fitting and securing of equipment. All sections have chamfered edges. The vertical frame sections have two depth/width - recessed mounting levels each, which can individually be used for flexible attachment of the installation components.

Enclosures are bayable on all sides: on the left, right, front and rear, at the top or round corners.

Basic enclosure already equipped with pre-configured, 100 mm high base/plinth corner pieces of the VX base/plinth system.

Base/plinth trims, side, solid and vented at the front are included with the supply for retrospective toolless assembly. This makes easy transportation to sites by lift trucks or forklifts possible.

Aluminium/sheet steel front door with a specific honeycomb perforation, vented surface area 85% perforated.

Framed in a frame of aluminium sections, with foamed-in seal, four-point locking rod, comfort handle for

semi-cylinder (30/10) mm, with security lock 3524.

Four hinges, with captive hinge pins, door opening angle with stand-alone siting 180°, door hinge may be swapped to opposite side without dismantling locking rods.

Sheet steel rear door, vented, vertically divided, for space-saving installation of the enclosures and easy access to the components. Specific honeycomb perforation, vented surface area 85% perforated. Doors with foamed-in seal. Main door with four-point locking rod, comfort handle for semi-cylinder (30/10) mm, with security lock 3524 E. Adjacent door with additional internal swing lever handle and two-point locking rod. Main and adjacent door with four hinges, hinges with captive hinge pins, door opening angle with stand-alone siting on both sides 180°.

Multi-piece roof plate for side cable entry via brush strips across the entire enclosure depth. Roof plate for retrofitting, removable despite already made cable routing. Cut-out for accommodating a fan module already integrated and closed by a cover. For supporting passive ventilation it is possible to raise the cover by means of spacers.

One-piece, lockable side panels with security lock 3524 E included with the supply. Optional internal latch available from the accessories range.

Base frame already equipped with installation rails for accommodating gland plates, pre-configured with one-part vented gland plate, including filter mat, with integral cable entry via brush strips at the rear.

Alternative base modules or function units may be exchanged from the range of accessories.

Pre-configured with two 482.6 mm (19") mounting frames, front and rear.

The static total load capacity of both mounting levels is 15,000 N.

Mounting frame consisting of universal mounting angles for server, network and electronic applications welded to a torsionally stiff all-round frame using horizontal connection sections. Depth-variable,

screw-fastened via the slot attachment with the horizontal frame of the enclosure rack.

Mounting frames, front and rear, including additional pitch pattern of holes (U centre attachment) according to standard EIA 310 E. All height units are labelled and numbered in the opposite direction on the front and rear mounting level. U labelling of mounting levels can be read from the outside for easy assembly. Mounting angles of front mounting frame, prepared for toolless accommodation of cable routing aids and organisation of structured cabling in maximum packaging density or for equipment with a sensor strip for automatic identification of the installed components by means of Radio Frequency Identification (RFID).

Mounting angles of rear mounting frame, prepared for accommodation of a Power Distribution Unit (PDU) in 1 U form factor on both sides for enclosure electrical power distribution, without waste of installation volume thanks to space-saving side mounting between mounting level and side panel in the Zero-U space.

Supply includes field-tested mounting assembly parts such as spacers for optional raising of the cover, levelling feet with adaptor sleeves for base/plinth assembly, 4 cable clamp rails for mounting on the outer mounting level, to fit enclosure depth, 10 metal cable shunting rings, assembly parts for 482.6 mm (19") installation components consisting of 50 multi-tooth screws, captive nuts with contacts and washers of thread size M5.

Enclosure design with pre-assembled central earthing point and tested potential equalisation of all components to EN 60950.

Material: „Sheet steel, aluminium

Base/plinth corner piece: Sheet steel

Base/plinth trim panel front/rear: Sheet steel

Corner and baying cover: Plastic

Surface finish: Panels, doors, RAL 7035, interior installation, base/plinth RAL 9005

Approvals: UL, cUL

Dimensions (WxHxD): 800x2000+100 x1000 mm

Model No.: TS IT 5509.161

Manufacturer: Rittal GmbH & Co. KG