

# Rittal – The System.

Faster – better – everywhere.



## DK 7063.752

## Slide rail, 1 U, depth-variable

State: 23.05.2026. (Source: [rittal.com/hr-hr](http://rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7063.752 - Slide rail, 1 U, depth-variable for VX IT, TE

For server and network enclosures with two 482.6 mm (19") mounting levels, for mounting both on cranked and L-shaped mounting angles, 482.6 mm (19") mounting frames and on TE, pull-out.



## Features

|                      |  |
|----------------------|--|
| Model No.            | DK 7063.752  |
| Product description  | For direct attachment to the 482.6 mm (19") system punchings on the mounting angles. The slide rails are pulled out to the required length and secured between the front and rear mounting level on the 482.6 mm (19") pitch pattern.  |
| Benefits             | No loss of U<br>Thanks to the thin support surface of only around 0.8 mm thickness, exceeding the U pitch pattern is generally avoided, provided the components do not exceed a maximum height of 43.5 mm. In this way, several units may be easily arranged on top of one another without offset. |
| Applications         | For mounting on the front mounting level   |
| Material             | Sheet steel  |
| Surface finish       | Zinc-plated  |
| Supply includes      | Assembly parts   |
| Installation options | For attachment between the front and rear 482.6 mm (19") mounting level  |
| Load capacity        | 20 kg static load  |
| Note                 | Effective contact surface 30 mm per side   |
| Contact surface      | Width: 30 mm   |

# Features

|                               |   |
|-------------------------------|---|
| Distance between levels       | 550 - 750 mm  |
| Packs of                      | 2 pc(s).  |
| Net weight                    | 2,558 kg  |
| Gross weight                  | 2,7 kg  |
| PCF per pack (cradle-to-gate) | 11.3 kg CO2 eq (Cat B)  |
| Note on PCF category          | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared                      |
| Customs tariff number         | 73269098  |
| ETIM 9                        | EC002625  |
| ECLASS 8.0                    | 27189234  |
| Product description           | DK Slide rail, Support surface Width: 30 mm, 1 U, depth-variable, 20 kg, static, distance between levels: 550-750 mm, For TS IT, TE |

# Tender text

Slide rails, depth-variable, 1 U

For server and network enclosures

with two 482.6 mm (19 inch) mounting levels,  
without additional loss of U.

For attachment on both cranked and L-shaped  
mounting angles and 482.6 mm (19 inch) mounting  
frames. The slide rails are pulled out to the  
required length and secured between the front  
and rear mounting level on the 482.6 mm (19 inch)  
pitch pattern.

Distance between 482.6 mm (19 inch) levels:

550 - 750 mm

Load capacity:

20 kg static load

Material:

Sheet steel, zinc-plated, passivated

Supply includes:

Packs of 2

Assembly parts