

Rittal – The System.

Faster – better – everywhere.



TX 5541.245 TX Colocation rack

State: 19.09.2025. (Source: rittal.com/hr-hr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TX 5541.245 - TX Colocation rack

The world of IT is changing, and the centralisation of IT in large data centres has become a long-term trend. The TX Colo, which is perfectly adapted to use in a large data centre, is our response. Thanks to its forward-thinking configuration, the TX Colo is ready for immediate use to suit your application!



Features

Model No.	TX 5541.245
Design	Standard
Material	Sheet steel
Surface finish	Enclosure frame: Dipcoat-primed Interior installation: Spray-finished Doors and roof: Dipcoat-primed, powder-coated Perforated Door, Sheet Steel
General colour	RAL 7035
Colour	Enclosure frame and roof: RAL 7035 Door: RAL 7035 Handle and hinges: RAL 9005

Features

Supply includes	<p>Enclosure frame with doors and roof plate</p> <p>Sheet steel front door, vented, 130° hinges</p> <p>Rear door made of sheet steel, divided, vented, 130° hinges</p> <p>Lock, front and rear: Comfort handle VX with numerical code</p> <p>Roof plate with cable entry across the full enclosure depth, left and right</p> <p>Divider panel, fitted to the left-hand side of the enclosure</p> <p>150 mm cable tray, fitted to the rear, right-hand side of the enclosure</p> <p>10 x captive nuts with screws (enclosed)</p> <p>Grounding accessories (supplied loose)</p> <p>Mounting angles, 482.6 mm (19")</p> <p>Air baffle plate</p> <p>Baying kit (supplied loose)</p>
Dimensions	<p>Width: 800 mm</p> <p>Height: 2,450 mm</p> <p>Depth: 1,200 mm</p>
Units	52 U
Distance between levels as delivered	745 mm
Distance between mounting levels min	115 mm
Distance between mounting levels max	341 mm
482.6 mm (19") attachment	800 mm-wide enclosure mounted on cross-members
Design	Standard
Roof design	Roof plate with cable entry across the full enclosure depth, left and right
Design doors	Vented doors
Rear door design	<p>Sheet steel door, vented</p> <p>two-piece</p> <p>Vented surface area approx. 78 % perforated</p>
Front door design	<p>Sheet steel door, vented</p> <p>Aluminium/sheet steel door, vented</p> <p>one-piece</p> <p>Vented surface area approx. 78 % perforated</p>

Features

Base design	Open
Mounting angles position	482.6 mm (19") level, front and rear
Load capacity	15.000 N
Note	Depending on how and where it is sited, the door opening angle may vary for selected applications
Packs of	1 pc(s).
Net weight	145
Gross weight	151
Customs tariff number	94032080
EAN	4028177971622
ETIM 9	EC002499
ETIM 8	EC002499
ECLASS 8.0	27180207

Approvals

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---