

# Rittal – The System.

Faster – better – everywhere.



## DK 7296.000

## Second pair of mounting angles

State: 23.05.2026. (Source: [rittal.com/hr-hr](http://rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7296.000 - Second pair of mounting angles for Data Rack

To accommodate 482.6 mm (19") network components or for the attachment of component shelves and slide rails.



## Features

|                         |  |
|-------------------------|--|
| Model No.               | DK 7296.000  |
| Product description     | To accommodate 482.6 mm (19") network components or for the attachment of component shelves and slide rails. 482.6 mm (19") punched profile at the front, hole centre distance 465 mm (470 mm at the rear), tailored to the attachment of patch panels and cable routing rails. The mounting level may be positioned on a 50 mm pitch pattern. Minimum distance between levels 150 mm, maximum distance between levels 350 mm. |
| Material                | Sheet steel, 2 mm  |
| Surface finish          | Spray-finished   |
| Colour                  | Profile frame: RAL 7035<br>Trim panel: RAL 5018  |
| Supply includes         | Torsionally stiff profile frame with 482.6 mm (19") punchings<br>Mounting accessories  |
| Installation dimensions | Installation depth for components: 482.6 mm<br>Installation width for components: 19"  |
| Units                   | 31 U   |
| Packs of                | 1 pc(s).   |
| Net weight              | 11,101 kg  |

# Features

|                               |  |
|-------------------------------|--|
| Gross weight                  | 11,685 kg  |
| PCF per pack (cradle-to-gate) | 44.5 kg CO2 eq (Cat B)   |
| Note on PCF category          | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number         | 94039910   |
| ETIM 9                        | EC002620   |
| ECLASS 8.0                    | 27189261   |
| Product description           | DK Second pair of mounting angles, 31 U, 482.6 mm (19"), For Data Rack   |

## Tender text

31 U mounting level for 482.6 mm (19") frame

31 U attachment level for 482.6 mm (19") frame, torsionally rigid extrusion frame, welded, made from 2 mm sheet steel, with integrated 482.6 mm (19") punchings as well as 25 mm DIN pitch pattern round and rectangular punchings. The additional attachment level is fixed to the folded sheet steel plinth in a 482.6 mm (19") frame.

Material: Sheet steel

Surface finish: RAL 7035

Height: 31 U