# Rittal – The System.

Faster – better – everywhere.





DK 7296.000


Second pair of mounting angles

State: 28.10.2025. (Source: rittal.com/hr-hr)



# DK 7296.000 - Second pair of mounting angles for Data Rack

To accommodate 482.6 mm (19") network components or for the attachment of component shelves and slide rails.



## **Features**

Model No.	DK 7296.000
Product description	To accommodate 482.6 mm (19") network components or for the attachment of component shelves and slide rails. 482.6 mm (19") punched profile at the front, hole centre distance 465 mm (470 mm at the rear), tailored to the attachment of patch panels and cable routing rails. The mounting level may be positioned on a 50 mm pitch pattern. Minimum distance between levels 150 mm, maximum distance between levels 350 mm.
Material	Sheet steel, 2 mm
Surface finish	Spray-finished
Colour	Profile frame: RAL 7035 Trim panel: RAL 5018
Supply includes	Torsionally stiff profile frame with 482.6 mm (19") punchings Mounting accessories
Installation dimensions	Installation depth for components: 482.6 mm Installation width for components: 19"
Units	31 U
Packs of	1 pc(s).
Net weight	11.101

© Rittal 2025

#### **Features**

11.685
44.5 kg CO2 eq (Cat B)
Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
94039910
4028177128798
E7282520
EC002620
27189261

### Tender text

31 U mounting level for 482.6 mm (19") frame

31 U attachment level for 482.6 mm (19") frame, torsionally rigid extrusion frame, welded, made from 2 mm sheet steel, with integrated 482.6 mm (19") punchings as well as 25 mm DIN pitch pattern round and rectangular punchings. The additional attachment level is fixed to the folded sheet steel plinth in a 482.6 mm (19") frame.

Material: Sheet steel Surface finish: RAL 7035

Height: 31 U

© Rittal 2025