

**Rittal – The System.**

Faster – better – everywhere.



**DK 7825.380**

**Gland plate modules, vented**

State: 10.02.2026. (Source: [rittal.com/hr-hr](http://rittal.com/hr-hr))



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# DK 7825.380 - Gland plate modules, vented for TS IT, TS, SE, TX CableNet

Gland plate modules, vented, for TS, TS IT, SE for use in the base frame of the network enclosure. Used in exchange for an existing gland plate of the same depth.

## Features

Model No.	DK 7825.380
Product description	Large perforated section for passive enclosure ventilation.
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Filter mat and nylon tape
Note	Several gland module plates need to be combined to close off the base completely in the TS-IT
Dimensions	Depth: 237.5 mm
To fit	Enclosure type: TS TS IT SE TX CableNet Width: 800 mm
Packs of	1 pc(s).
Net weight	1.95
Gross weight	2.26
PCF per pack (cradle-to-gate)	8.2 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	94039910
EAN	4028177233348
ETIM 9	EC002620
ECLASS 8.0	27189261

# Tender text

Gland plate module, vented  
For W: 800 mm,  
Depth: 237,5 mm  
For TS, TS IT, SE, TX CableNet  
For cable entry with brush  
Sheet steel, vented