


Rittal – The System.

Faster – better – everywhere.



DK 7856.220 PSM socket modules

State: 23.08.2025. (Source: rittal.com/hr-hr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7856.220 - PSM socket modules

The various modules may be inserted into the support rail in any combination.

Features

| | |
|-----------------------------------|--|
| Model No. | DK 7856.220 |
| Design | non-switchable |
| Product description | The modular system facilitates basic configuration of the racks, thanks to a vertical support rail with single-/3-phase infeed. The various socket modules to supply the active components may be snap-fitted into the support rail. The various modules, earthing pins, IEC320 etc. may be inserted into the support rail in any combination. This is easily achieved, even by non-electricians, thanks to the shock hazard protected plug & play system. |
| Material | Section: Aluminium, anodised Socket inserts: Plastic (PA6 GF 30 V1) |
| Length | 250 mm |
| Type of electrical connection | WAGO WINSTA MIDI |
| Phases per infeed | 1~ |
| Thermal overcurrent protection | per socket |
| Rated operating voltage | 110 V – 230 V AC, 50/60 Hz |
| Rated current (max.) | 16 A |
| Required number of module slots | 1 |
| Dimensions | Length: 250 mm |
| Operating temperature range | 5 °C...45 °C |
| Ambient humidity (non-condensing) | 5...95 % |
| Sockets | 4 x IEC 320 socket C13 |
| Packs of | 1 pc(s). |
| Net weight | 0.35 |

Features

| | |
|-----------------------|---------------|
| Gross weight | 0.36 |
| Customs tariff number | 85369001 |
| EAN | 4028177438842 |
| ETIM 9 | EC000330 |
| ECLASS 8.0 | 27142604 |

Approvals

| | |
|--------------|---------------------------|
| Approvals | IEC CB VDE |
| Explanations | Declaration of conformity |

Tender text

Power system module plug-in module, 4 x ICE, IEC 320 C13 with 10A single fuse

Installation via plug & play:

The plug-in module is locked into the power system module busbar. It can be locked in or unlocked whilst working. The module connection direction determines which power supply will be used.

A mixture of all of the modules can be fitted in the rails.

Technical fittings:

The plug-in module has 4 x IEC320 C13 sockets available for use. The module has integrated 10A circuit breakers for each socket. They protect all 4 sockets. The automatic circuit breaker can be reset for switching back on if it trips out.

Technical specifications:

Single-phase voltage range: 110V - 230V AC 50/60 Hz,
neutral conductor is required

Max. current per module: 10A at 230V AC, 15A at 110V AC

Temperature application range: +5°C - +45°C

Humidity range: 5% - 95% relative humidity,
non-condensing

Protection category IP20

W x H x D [mm]: 50 x 250 x 45