

Rittal – The System.

Faster – better – everywhere.



TS 8609.040 Divider panel

State: 23.05.2026. (Source: rittal.com/hr-hr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8609.040 - Divider panel for TS

For shielding individual enclosure cells. Thanks to the symmetry of the frame system, the divider panel can also be used at the rear.



Features

Model No.	TS 8609.040
Product description	For shielding individual enclosure cells. All-round, double fold for stability and to hold the seal. Thanks to the symmetry of the enclosure frame, divider panels may also be fitted at the rear, dimensions permitting.
Applications	Notches in the corners and half-way up the sides permit the use of angular baying brackets and baying brackets, even with a divider panel fitted.
Material	Sheet steel, 1.5 mm
Surface finish	Zinc-plated
Supply includes	Assembly parts
To fit	Enclosure type: TS 8 Height: = 2,000 mm Depth: = 400 mm
Installation options	For mounting on the outer mounting level This leaves the inner level free for further population
Assembly instruction	The divider panel may also be fitted at the rear. This allows, e.g. frequency converters for heat dissipation to be installed in a divider panel with the cooling units facing outwards and protected/finished off with a cover.

Features

IP protection category to IEC 60529	IP 54
Packs of	1 pc(s).
Net weight	8,471 kg
Gross weight	8,905 kg
Customs tariff number	94039910
ETIM 9	EC002525
ECLASS 8.0	27182102
Product description	TS Divider panel, for TS, for WD: 2000x400 mm