# Rittal – The System.

Faster – better – everywhere.





# TS 8626.500 Baying systems TS 8

State: 04.11.2025. (Source: rittal.com/hr-hr)



## TS 8626.500 - Baying systems TS 8

The TS 8 sheet steel baying system, with its symmetrical profile in the width and depth, offers a significant space gain, plus simple interior installation. This likewise ensures bayability from all sides. Additionally, the integral, automatic potential equalisation of all enclosure panels and the triple surface treatment ensure optimum safety.



## **Features**

Model No.	TS 8626.500
Material	Enclosure frame: Sheet steel, 1.5 mm
	Roof: Sheet steel, 1.5 mm
	Door: Sheet steel, 2.0 mm
	Rear panel: Sheet steel, 1.5 mm
	Gland plates: Sheet steel, 1.5 mm
	Mounting plate: Sheet steel, 3.0 mm
Surface finish	Enclosure frame: Dipcoat-primed
	Door, roof and rear panel: Dipcoat-primed, powder-coated on the
	outside, textured paint
	Mounting plate and gland plates: Zinc-plated
Colour	RAL 7035

## **Features**

Supply includes	Enclosure frame Door(s) R/h door hinge with single-door enclosures, may be swapped to opposite side Roof plate Rear panel 4 eyebolts Lock: 3 mm double-bit Gland plates Mounting plate 2 TS punched rails 18 x 38 mm 2 support strips fitted in the enclosure depth
Dimensions	Width: 600 mm Height: 2,200 mm Depth: 600 mm
Dimensions mounting plate (W x H)	499 mm x 2,096 mm
Protection category to IEC 60 529	IP 55
Protection category NEMA	NEMA 1 NEMA 12
Type rating to UL 50E	Type 1 Type 12
IK Code	IK09
Number of doors	1
2 supportstrips in depth	Yes
Basic material	Sheet steel
Packs of	1 pc(s).
Net weight	230.159
Gross weight	241.182
Customs tariff number	7326908688
EAN	4028177250963
EAN11 (UC)	38026

## Features

ETIM 9	EC000261
ECLASS 8.0	27180101

# **Approvals**

Approvals	Bureau Veritas Lloyds Register of Shipping UL + C-UL (listed)
Certificates	Surface finish
Explanations	Manufacturer's declaration  Declaration of conformity  Declaration of conformity UK

© Rittal 2025

## Tender text

Enclosure (baying system) single-door Enclosure:

Symmetrical frame construction of rolled hollow sections with holes on a 25 mm DIN pitch pattern.

All sections have chamfered edges.

The horizontal sections have an additional protection lip above the seal.

The vertical sections have two mounting levels for space-saving interior installation.

Bayable on all sides.

Four eyebolts, three-piece gland plate can be removed and interchanged, fitted.

#### Door:

2 mm sheet steel, with foamed-in seal, with removable tubular door frame with holes on a 25 mm DIN pitch pattern, 4-point latch locking rod, double-bit insert to DIN 43668.

Door hinge may be swapped from right to left. Hinges with captive hinge pins, door opening angle 130° to VDI, can be retrofitted to 180°, floor clearance 25 mm.

Rear panel and roof plate: With foamed-in seal, removable

#### Mounting plate:

C-folded on the sides, depth-adjustable via integral plastic sliders in a 25 mm pitch pattern.

All screw-fastened cover parts with automatic potential equalisation and prepared for the attachment of earthing straps.

#### Accessories:

Side panels with foamed-in seal and assembly screws for finishing off the sides.

Protection category: IP 55

## Material:

1.5 mm sheet steel, mounting plate of 3 mm sheet steel, zinc-plated

#### Surface finish:

Electrophoretic dipcoat-primed
Outside surfaces powder-coated in textured RAL 7035

Dimensions (W x H x D): 600 x 2200 x 600 mm