

Rittal – The System.

Faster – better – everywhere.



TS 8611.070 Comfort handle

State: 22.05.2026. (Source: rittal.com/hr-hr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8611.070 - Comfort handle for TS, TS IT, VX SE, PC, IW

Thanks to its folding action, the handle does not take up any swing space, thus maximising the door surface area available for installed equipment. Simple assembly, thanks to the snap-mounted handle system.



Features

| | |
|----------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Model No. | TS 8611.070 |
| Design | for profile half-cylinder |
| Product description | As the handle does not take up any swing space, due to its folding mechanism, the door surface area may be maximised for installed equipment. |
| Material | Die-cast zinc |
| Surface finish | Powder-coated |
| Colour | RAL 7035 |
| Assembly instruction | The handle adaptor is required for mounting on glazed door TS, VX SE, lower door PC, designer door IW |
| Lock | Lock version: Prepared for the installation of profile semi-cylinders with an overall length of 40 or 45 mm (to DIN 18 252) or lock and push-button inserts with a length of 40 mm. |

Features

| | |
|-----------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| To fit enclosure type | TS TS IT VX SE PC enclosure door IW TS 8 bayed enclosure suites with comfort handle SE stainless steel EL 3-part, 18 – 21 U AX wall-mounted enclosure, 3-part |
| Packs of | 1 pc(s). |
| Net weight | 0,53 kg |
| Gross weight | 0,58 kg |
| Customs tariff number | 83024110 |
| ETIM 9 | EC000327 |
| ECLASS 8.0 | 27409217 |
| Product description | TS Comfort handle, for TS, TS IT, SE, PC, IW, for semi-cylinder, RAL 7035 |