

Rittal – The System.

Faster – better – everywhere.



VX 8660.009

Base/plinth corner pieces with
base/plinth trim panels, front and
rear

State: 06.02.2026. (Source: ittal.com/hr-hr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8660.009 - Base/plinth corner pieces with base/plinth trim panels, front and rear for base/plinth system VX, sheet steel

Base/plinth corner pieces with trim panels for flexible cable entry.



Features

Model No.	VX 8660.009
Benefits	<p>Reliable – Excellent stability of the base/plinth</p> <p>Flexible – Countless interior installation options with VX accessories</p> <p>Simple – Flush termination between the baying points</p>
Material	<p>Base/plinth corner piece: Sheet steel</p> <p>Base/plinth trim panel front/rear: Sheet steel</p> <p>Corner and baying cover: Plastic</p>
Colour	RAL 9005
Supply includes	<p>4 corner covers</p> <p>Assembly parts</p> <p>4 base/plinth corner pieces, 100 mm high</p> <p>2 base/plinth trim panels, front/rear, 100 mm high</p>
Note	Side base/plinth trim panels finish off a base/plinth unit or provide additional stabilisation between base/plinths or enable interior configuration of the base/plinth
Dimensions	Height: 100 mm

Features

To fit	Enclosure type: VX VX IT VX SE TX CableNet TS TS IT TP PC IW CX Width: = 1,800 mm
Type rating to UL 50E	Type 1 Type 12
Weight/pack	9,55 kg
Packs of	2 pc(s).
Net weight	9.546
Gross weight	9.55
PCF per pack (cradle-to-gate)	36.4 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	94039910
EAN	4028177978102
ETIM 9	EC000721
ETIM 8	EC000721
ECLASS 8.0	27182003

Approvals

Approvals	UL + C-UL - FTTA
Explanations	PCF-declaration
