Rittal - The System.

Faster – better – everywhere.





VX 8660.031 Base/plinth trim panels, side

State: 04.11.2025. (Source: rittal.com/hr-hr)



VX 8660.031 - Base/plinth trim panels, side for base/plinth system VX, sheet steel

To finish off a base/plinth unit at the sides and for additional stability or interior configuration of bayed base/plinths. One 200 mm high or two 100 mm high trim panels may optionally be fitted on 200 mm high base/plinths.







Features

Model No.	VX 8660.031
Design	Solid
Material	Sheet steel
Colour	RAL 9005
Supply includes	Assembly parts
Dimensions	Height: 100 mm
To fit	Enclosure type: VX
	VX IT
	VX SE
	TX CableNet
	TS
	TS IT
	TP
	PC
	IW
	CX
	Depth: = 400 mm

© Rittal 2025 2

Features

Type rating to UL 50E	Type 1
	Type 12
Weight/pack	1,11 kg
Packs of	2 pc(s).
To fit	for base/plinth system VX, sheet steel
Net weight	1
Gross weight	1.152
PCF per pack (cradle-to-gate)	4.2 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Custome to wiff number	
Customs tariff number	94039910
EAN	4028177978218
ETIM 9	EC000721
ETIM 8	EC000721
ECLASS 8.0	27182003

Approvals

|--|

© Rittal 2025 3