


Rittal – The System.

Faster – better – everywhere.



KEL 9306.000 Ex enclosures

State: 17.09.2025. (Source: [rittal.com/hr-hr](https://www.rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



KEL 9306.000 - Ex enclosures Stainless steel, empty enclosure with screw fastened cover

Ex enclosure with screw-fastened cover, stainless steel



Features

| | |
|-----------------|---|
| Model No. | KEL 9306.000 |
| Design | Ex enclosures |
| Applications | Zone 1 and 2 or 21 and 22 to 2014/34/EC Ambient temperature range: -30 °C...+80 °C The specified temperatures may be limited by the installed equipment Explosion protection category to EN 60 079: Equipment protection thanks to increased safety (Ex e), equipment protection thanks to enclosure (Ex tb) |
| Material | Enclosure: Stainless steel 1.4301 (AISI 304) Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in silicone seal |
| Surface finish | Enclosure: Brushed, grain 400, peak-to-valley height < 0.8 µm |
| Supply includes | Enclosure Cover |
| Dimensions | Width: 300 mm Height: 300 mm Depth: 120 mm |

Features

| | |
|--------------------------------------|-----------------------------------|
| Certificate IEC EX PTB 09.0033U | Yes |
| Certificate PTB 03 ATEX 1013U | Yes |
| Basic material | Stainless steel 1.4301 (AISI 304) |
| IP protection category to IEC 60 529 | IP 66 |
| Packs of | 1 pc(s). |
| Net weight | 3.7 |
| Gross weight | 3.9 |
| Customs tariff number | 94032080 |
| EAN | 4028177138643 |
| ETIM 9 | EC002503 |
| ECLASS 8.0 | 27180502 |

Approvals

| | |
|-----------|----------------|
| Approvals | ATEX IEC Ex |
|-----------|----------------|