

Rittal – The System.

Faster – better – everywhere.



SV 9340.520 OM adaptors

State: 16.07.2025. (Source: rittal.com/hr-hr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9340.520 - OM adaptors with spring terminals



Features

| | |
|---|--|
| Model No. | SV 9340.520 |
| Material | Polyamide Fire protection corresponding to UL 94-V0 |
| Colour | Chassis: RAL 7035 |
| Rated current max. | 32 A |
| Rated operating voltage | 690 V, 3~ |
| For bar systems with centre-to-centre spacing | 60 mm |
| Support rail type | TS 45D |
| Number of poles | 3-pole |
| Dimensions | Width: 45 mm Height: 208 mm |
| Connection of round conductors | 1.5 - 6 mm ² |
| Support rails Qty/height | 2 / 10 mm |
| To fit busbars | Height: 5, 10 mm |
| Packs of | 1 pc(s). |
| Net weight | 0.238 |
| Gross weight | 0.266 |
| Copper weight (kg per piece) | 0.027 |

Features

| | |
|-----------------------|---------------|
| Customs tariff number | 85369095 |
| EAN | 4028177630710 |
| ETIM 9 | EC001531 |
| ECLASS 8.0 | 27370304 |

Approvals

| | |
|--------------|---|
| Approvals | ABS DNV-GL Lloyds Register of Shipping |
| Explanations | Declaration of conformity Declaration of conformity UK |
