


Rittal – The System.

Faster – better – everywhere.



RX 9360.110

RiLineX basic module

State: 09.02.2026. (Source: rittal.com/hr-hr)



FRIEDHELM LOH GROUP

RX 9360.110 - RiLineX basic module

RiLineX basic module, 3-pole, width 100 mm, with integrated busbar support suitable for top mounting, for the modular RiLineX board. Supports the integration of flat bars from 15 x 5 mm to 30 x 10 mm. End-to-end contact hazard protection up to IP 2XB, upgradable to IP 3X. The basic module comprises a base section including busbar support and a top section for contact hazard protection. When compiling a complete solution from basic modules, end modules are additionally required.



Features

Model No.	RX 9360.110
Benefits	<ul style="list-style-type: none">Scalable system lengths with basic modulesSimple assemblyScalable rated currents thanks to variable busbar cross-sectionsTested short-circuit resistance up to 65 kASuitable for applications up to 1000 V AC and up to 1500 V DCExtensive range of system accessoriesContact hazard protection up to IP 2XB, upgradable to IP 3XTested and certified to IEC and ULSimple extension and baying
Material	<ul style="list-style-type: none">Polyamide (PA 6)Fire protection corresponding to UL 94
Colour	<ul style="list-style-type: none">RAL 35745RAL 9005
Supply includes	<ul style="list-style-type: none">Basic module base sectionBasic module (contact hazard protection cover)Assembly screws

Features

IP protection category to IEC 60529	IP 2XB
Standards	IEC/EN 61439-1 UL 508
Rated current max.	800 A
Note	Busbars are not included with the supply
Electrical ratings UL (SCCR)	65 kA - 600 V, RMS, unprotected 100 kA - 600 V, Fuse Class L max. 1600 A, JDDZ/7 100 kA - 480 V, circuit breaker max. 800 A, DIVQ/7 65 kA - 600 V, circuit breaker max. 800 A, DIVQ/7
Centre-to-centre spacing of busbars	60 mm
Rated impulse withstand voltage Uimp	12 kV
Rated voltage	1.000 V AC 600 V AC (UL) 1.500 V DC 600 V DC (UL)
Rated insulation voltage Ui	1.000 V AC 1.500 V DC
Rated short-term withstand current/t	65 kA/500 ms
Overvoltage category	4
Contamination level	3
Number of poles	3-pole
Fundamental frequency	50...60 Hz
Ambient humidity (non-condensing)	10...90 %
To fit busbars	15 x 5/10 20 x 5/10 30 x 5/10
Operating temperature range	-5 °C...55 °C

Features

Storage temperature range	-25 °C...75 °C
Dimensions	Width: 100 mm Height: 246 mm Depth: 49.2 mm
Packs of	6 pc(s).
Net weight	3
Gross weight	3.292
Customs tariff number	85369010
EAN	4028177997295
ETIM 9	EC001900

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity