

# Rittal – The System.

Faster – better – everywhere.



## SV 9340.710 OM adaptors

State: 03.07.2026. (Source: [rittal.com/hr-hr](http://rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9340.710 - OM adaptors with connection cables



## Features

|   |   |
|---|---|
| Model No.                                     | SV 9340.710   |
| Design  | With connection cable   |
| Material                                      | Polyamide<br>Fire protection corresponding to UL 94-V0  |
| Colour  | Chassis: RAL 7035   |
| Connection cables (AWG)                       | AWG 8   |
| Rated current max.                            | 40 A  |
| Rated operating voltage                       | 690 V, 3~   |
| Note  | The technical data may vary for UL applications   |
| Electrical ratings UL (SCCR)                  | 30 kA - 600 V, Fuse Class K5 max. 60 A, JDDZ/7<br>30 kA - 480 V, Combination Motor Controller max. 63 A, NKJH/7<br>65 kA - 600 V, Fuse Class J max. 60 A, JDDZ/7<br>65 kA - 480 V, Manual Motor Controller max. 63 A, NLRV/7<br>65 kA - 480 V, Combination Motor Controller max. 63 A, NKJH/7 |
| For bar systems with centre-to-centre spacing | 60 mm   |
| Length of connection cable                    | 130 mm  |
| Support rail type                             | without support frame, 2 x 7.5 x 35 mm  |
| Number of poles                               | 3-pole  |
| Dimensions                                    | Width: 75 mm<br>Height: 208 mm  |

# Features

---

|                              |   |
|------------------------------|---|
| Support rails Qty/height     | 2 / 7.5 mm  |
| To fit busbars               | Height: 5, 10 mm  |
| Approvals                    | UL  |
| Packs of                     | 1 pc(s).  |
| Net weight                   | 0,379 kg  |
| Gross weight                 | 0,396 kg  |
| Copper weight (kg per piece) | 0,088   |
| Customs tariff number        | 85369095  |
| ETIM 9                       | EC001531  |
| ECLASS 8.0                   | 27370304  |
| Product description          | SV OM adaptor, 40 A, 690 V, 3-pole, connection cable AWG 8, WH: 75x208 mm, 2 insert strips, 2 metal support rails |

# Approvals

---

|              |   |
|--------------|---|
| Approvals    | ABS<br>DNV<br>Lloyds Register<br>UL + C-UL (listed)       |
| Explanations | Declaration of conformity<br>Declaration of conformity UK |

# Tender text

OM adaptor 40 A

OM adaptor 40 A with connection cable, 3-pole,  
for busbar thickness 5/10 mm and PLS 800/1600

Technical specifications

Connection cable: AWG 8 / approx. 10 qmm

Construction width: 75 mm

Length: 208 mm

Support frame: -mm

Support frame support: -

Insert strips: -

Support rail: 2

System:

Rittal RiLine60