Rittal - The System.

Faster – better – everywhere.





RX 9360.535 RiLineX CB component adaptor

State: 03.11.2025. (Source: rittal.com/hr-hr)



RX 9360.535 - RiLineX CB component adaptor

RiLineX CB component adaptor (3-pole, max. 630 A) for 60 mm busbar systems. The device width is 140 mm. The "Easy-Fix" concept allows adaptors and switches to be mounted independently of one another. This concept is available for all popular manufacturers. The adaptor features tool-free snap-on mounting with semi-automatic adjustment of the bar thickness between 5 and 10 mm. The cable outlet is easily converted to the top or bottom to suit individual requirements.



Features

| Model No. | RX 9360.535 |
|---|---|
| Design | Easy Fix |
| Benefits | Direct mounting of moulded-case circuit-breakers (MCCBs) on the board Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Fast, simple pre-assembly of standard market switch types outside of the enclosure |
| Material | Polyamide (PA 6) Fire protection corresponding to UL 94 |
| Colour | RAL 9005 RAL 35745 |
| Supply includes | 3 terminal covers |
| IP protection category to IEC 60 529 | IP 2XB |
| Rated impulse withstand voltage Uimp | 12 kV |
| | |

© Rittal 2025 2

Features

| Rated voltage | 690 V AC 690 V DC 600 V AC (UL) |
|---------------------------------------|--|
| Rated insulation voltage | 1.000 V |
| Overvoltage category | 4 |
| Contamination level | 3 |
| Number of poles | 3-pole |
| Cable outlet | Top/bottom |
| Type of electrical connection | Screw M10 |
| To fit manufacturer (model) | ABB (S5 400, S5, T5, XT5, FG400, FG630) Chint (NM8N-400, NM8N-630, NXM-400S, NXM-630S, NXMS-400, NXMS-630) Eaton (NZM3) Fuji Electric (BW4003) Hager (X630) Hyundai Electric (400AF, 400, 630AF) LS Electric (400AF, TS400, TS630) Mitsubishi (NF400-SW, NF630-SW) OEZ (BH630) Rockwell (140G-K0F3-D40, 140G-M0F3-D63) Schneider (NSX400, NSX630) Schrack (MC3) Siemens (3VA23, 3VA24) Terasaki (S400, E630, S630) |
| To fit busbar system | RiLineX RiLine60 |
| Fundamental frequency | 5060 Hz |
| Ambient humidity (non- condensing) | 1090 % |
| To fit busbars | 15 x 5/10 |
| | 20 x 5/10 30 x 5/10 |
| Operating temperature range | |

© Rittal 2025 3

Features

| Dimensions | Width: 145 mm Height: 325 mm |
|------------------------------|---------------------------------|
| Packs of | 1 pc(s). |
| Net weight | 5 |
| Gross weight | 5.206 |
| Copper weight (kg per piece) | 2.64 |
| Customs tariff number | 85369095 |
| EAN | 4028177997110 |
| ETIM 9 | EC001531 |

Approvals

| Approvals | UL + C-UL (listed) |
|--------------|---------------------------|
| Explanations | Declaration of conformity |

© Rittal 2025