Rittal – The System.

Faster – better – everywhere.





SV 9342.224 Connection adaptor

State: 31.10.2025. (Source: rittal.com/hr-hr)



SV 9342.224 - Connection adaptor

For bar systems with 60 mm centre-to-centre spacing.

Features

Model No.	SV 9342.224
Material	Cover: ABS Punched section: Polyamide Fire protection corresponding to UL 94-V0
Colour	RAL 7035
Rated current max.	125 A
Rated operating voltage	690 V, 4~
Electrical ratings UL (SCCR)	50 kA - 600 V, Fuse Class K5 max. 125 A, JDDZ/7 65 kA - 480 V, circuit breaker max. 125 A, DIVQ/7 65 kA - 600 V, Fuse Class J max. 400 A, JDDZ/7
Cable outlet	Top/bottom
For bar systems with centre-to- centre spacing	60 mm
Note	The technical data may vary for UL applications UL approval only applies in conjunction with AC application The rated operating voltage for DC applications depends on the busbar arrangement in the busbar supports 9340.050/9341.050/9342.050.
Number of poles	4-pole
Dimensions	Width: 75 mm Height: 270 mm
Connection of round conductors, fine wire with wire end ferrule	10 - 25 mm²
Connection of round conductors, multi-wire	16 - 35 mm²
To fit busbars	Height: 5, 10 mm

© Rittal 2025

Features

Clamping area for laminated copper bars (W x H)	10 x 7.8 mm
Packs of	1 pc(s).
Net weight	0.199
Gross weight	0.632
Copper weight (kg per piece)	0.07
Customs tariff number	85369010
EAN	4028177536807
ETIM 9	EC001531
ECLASS 8.0	27370304

Approvals

Approvals	ABS
	DNV-GL
	Lloyds Register of Shipping
	UL + C-UL (listed)
Explanations	Declaration of conformity
	Declaration of conformity UK

© Rittal 2025 3