

# Rittal – The System.

Faster – better – everywhere.



## RX 9360.000 RiLineX baying set

State: 22.05.2026. (Source: [rittal.com/hr-hr](http://rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# RX 9360.000 - RiLineX baying set for board

RiLineX baying connector set for the 3-pole complete board, for use with 550 A and 800 A. Comprising a busbar connector and contact hazard protection cover. For simple baying of boards between two bayed VX enclosures, no drilling required.



## Features

Model No.	RX 9360.000
Benefits	Time savings thanks to fully digital product data Reduced assembly time thanks to pre-assembled complete board Tested short-circuit resistance up to 65 kA Suitable for applications up to 1000 V AC and up to 1500 V DC Tested and certified to IEC and UL Simple extension and baying
Material	Upper part: Sheet steel, zinc-plated Contact plate: E-Cu, tin-plated Front cover: Polyamide (PA 6) Fire protection corresponding to UL 94
Colour	RAL 35745
Supply includes	3 busbar connectors 1 front cover 1 insulating plate
IP protection category to IEC 60529	IP 2XB
Standards	IEC 61 439-1/-2 UL 508

# Features

Rated current max.	780 A
Rated current (UL)	780 A
Electrical ratings UL (SCCR)	52.5 kA - 600 V, RMS, unprotected 100 kA - 600 V, Fuse Class L max. 1600 A, JDDZ/7 100 kA - 600 V, circuit breaker max. 600 A, DIVQ/7 100 kA - 480 V, circuit breaker max. 800 A, DIVQ/7 65 kA - 600 V, circuit breaker max. 800 A, DIVQ/7
Rated impulse withstand voltage U <sub>imp</sub>	12 kV
Rated voltage	1.000 V AC 1.500 V DC 600 V AC (UL) 600 V DC (UL)
Rated insulation voltage U <sub>i</sub>	1.000 V AC 1.500 V DC
Rated impulse withstand current	103 kA 115,5 kA
Rated short-term withstand current/t	45 kA/200 ms 52.5 kA/500 ms
Overvoltage category	4
Contamination level	3
Number of poles	3-pole
To fit Model No.	9360004 9360008 9360024 9360028 9360064 9360068 9360084 9360088
Fundamental frequency	50...60 Hz
Ambient humidity (non- condensing)	10...90 %
To fit busbars	30 x 5/10

# Features

---

Operating temperature range	-5 °C...55 °C
Dimensions	Width: 154 mm Height: 240 mm Depth: 77 mm
Packs of	1 pc(s).
Net weight	1,88 kg
Gross weight	1,924 kg
Copper weight (kg per piece)	0,297
PCF per pack (cradle-to-gate)	10.32
Customs tariff number	85369010
ETIM 9	EC002270
Product description	RiLineX baying connector set for the complete board, for use with 550 A and 800 A. Comprising a busbar connector and contact hazard protection cover. For simple, no-drill baying of boards between two bayed enclosures. Baying connectors are included with the supply.

# Approvals

---

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity PCF-declaration

# Tender text

RiLineX baying set for board

Baying connector set for the complete board, for use with 550 A and 800 A. Comprising a busbar connector and contact hazard protection cover. For simple baying of boards between two bayed enclosures,

no drilling required.

Tested short-circuit resistance up to 65 kA.

IEC and UL approved.

Product information

Number of poles: 3

Busbar dimensions: 30 mm x 5/10 mm

Rated current max.: 550/800 A

Dimensions: 154 mm x 240 mm x 77 mm (WxHxD)

Manufacturer: Rittal GmbH & Co. KG

Type: 9360000