

Rittal – The System.

Faster – better – everywhere.



RX 9360.512

RiLineX CB component adaptor

State: 27.05.2026. (Source: rittal.com/hr-hr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.512 - RiLineX CB component adaptor

This new product is currently unavailable. Alternatively, you can use the item number 9360.612.



Features

Model No.	RX 9360.512
Design	Easy Fix
Benefits	Direct mounting of moulded-case circuit-breakers (MCCBs) on the board Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Fast, simple pre-assembly of standard market switch types outside of the enclosure
Material	Polyamide (PA 6) Fire protection corresponding to UL 94
Colour	RAL 9005 RAL 35745
Supply includes	3 connection space covers
IP protection category to IEC 60529	IP 2XB
Rated impulse withstand voltage Uimp	8 kV
Rated voltage	690 V AC 600 V AC (UL)

Features

Rated insulation voltage Ui	1.000 V
Contamination level	3
Clamping area for laminated copper bars (W x H)	15 x 6 mm
Number of poles	3-pole
Cable outlet	Bottom
Type of electrical connection	Screw M8
To fit manufacturer (model)	ABB (S3 150, S3 225, S3, T3, T4, XT3, XT4, FE160, FE250) Chint (NM8N-250, NM1-250H, NXM-250S, NXMS-250) Eaton (LZMB2-A160, LZMB2-A250) Fuji Electric (BW160_-3P, BW250_-3) Hager (P250) Himel (HDM3-160, HDM3-250, HDM3L-160, HDM3L-250) Hyundai Electric (160, 250AF) Legrand (DPX250, DPX ³ 250) LS Electric (250AF, TS250) Mitsubishi (NF125-SGV, NF160-SGV, NF250-SV) OEZ (BD250) Rockwell (140G-J0F3-D25) Sassin (3SM8N-225, 3SM8L-225) Schneider (EZC250H, NS100, NS160, NS250, NSX100, NSX160, NSX250, GV5) Schrack (MC2) Siemens (3VA20, 3VA21, 3VA22, 3VT2, 3RV1063, 3RV1363, 3RV1364, VL160/3VL2) Terasaki (S160, S250, H250)
To fit busbar system	RiLineX RiLine60
Fundamental frequency	50...60 Hz
Ambient humidity (non-condensing)	10...90 %
To fit busbars	15 x 5/10 20 x 5/10 30 x 5/10
Operating temperature range	-25 °C...55 °C

Features

Storage temperature range	-25 °C...75 °C
Dimensions	Width: 105 mm Height: 252 mm Depth: 63 mm
Packs of	1 pc(s).
Net weight	1,7 kg
Gross weight	1,792 kg
Copper weight (kg per piece)	0,608
PCF per pack (cradle-to-gate)	10.84
Customs tariff number	85369095
ETIM 9	EC001531
Product description	RiLineX CB component adaptor (3-pole, max. 250 A) for 60 mm busbar systems. The device width is 105 mm. The "Easy-Fix" concept allows adaptors and switches to be mounted independently of one another. This concept is available for all popular manufacturers. The adaptor features tool-free snap-on mounting. Version for cable outlet at the bottom.

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity PCF-declaration