

# Rittal – The System.

Faster – better – everywhere.



## RX 9360.798

## RiLineX component adaptor

State: 04.09.2025. (Source: [rittal.com/hr-hr](https://www.rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# RX 9360.798 - RiLineX component adaptor

RiLineX component adaptor (80 A, 3-pole, including connection cables) in width 72 mm for RiLineX and other 60 mm busbar system platforms. With integral threaded inserts. Sample for standard commercially available circuit-breakers.



## Features

|   |  |
|---|--|
| Model No.                                     | RX 9360.798  |
| Design  | With connection cable  |
| Benefits                                      | For mounting equipment for top hat rail installation, e.g. motor starter<br>Pre-assembled connection cable<br>Simple clip locking for support rails<br>Optional anti-slip guard<br>Snap-on mounting and simple adjustment for busbar thickness (5/10 mm)<br>Simple assembly<br>Coordinated accessories reduce the number of different items required |
| Material                                      | Polyamide (PA 6)<br>Fire protection corresponding to UL 94   |
| Colour  | RAL 9005<br>RAL 35745  |
| Connection cables (AWG)                       | AWG 4  |
| Rated current max.                            | 80 A   |
| Cable outlet                                  | Top  |
| For bar systems with centre-to-centre spacing | 60 mm  |

# Features

|                                      |  |
|--------------------------------------|--|
| Number of poles                      | 3-pole   |
| To fit busbar system                 | RiLineX<br>RiLine60                            |
| Dimensions                           | Width: 72 mm<br>Height: 240 mm<br>Depth: 37 mm |
| To fit busbars                       | 15 x 5/10<br>20 x 5/10<br>30 x 5/10            |
| Rated voltage                        | 690 V AC<br>600 V AC (UL)<br>600 V DC (UL)     |
| Overvoltage category                 | 4  |
| Contamination level                  | 3  |
| Standards                            | IEC 61 439-1/-2<br>UL 508                      |
| IP protection category to IEC 60 529 | IP 2XB   |
| Operation humidity max               | 90 %   |
| Operating temperature range          | -5 °C...55 °C                                  |
| Storage temperature range            | -25 °C...75 °C                                 |
| Ambient humidity (non-condensing)    | 10...90 %                                      |
| Packs of                             | 1 pc(s).                                       |
| Net weight                           | 0.7  |
| Gross weight                         | 0.702  |
| Copper weight (kg per piece)         | 0.246  |
| Customs tariff number                | 85369095                                       |
| ETIM 9                               | EC001531                                       |

# Approvals

|              |                           |
|--------------|---------------------------|
| Approvals    | UL + C-UL (listed)        |
| Explanations | Declaration of conformity |