

Rittal – The System.

Faster – better – everywhere.



RX 9362.005

RiLineX NH fuse-switch disconnector

State: 04.02.2026. (Source: ittal.com/hr-hr)



RX 9362.005 - RiLineX NH fuse-switch disconnector

RiLineX NH fuse-switch disconnector in size 00 for 60 mm busbar systems. The cover can be locked and prepared for a lead seal. It also has visual fuse monitoring. Integrated measuring points on the cover ensure safe voltage testing. NH fuse-switch disconnectors have a park position to make maintenance easier. Size M8 screw terminal connection. Cable outlet can be at the top or bottom, as required. Includes electronic fuse monitoring.



Features

| | |
|---|--|
| Model No. | RX 9362.005 |
| Design | For 60 mm busbar systems |
| Benefits | <p>Cover: can be locked and prepared for a lead seal</p> <p>Voltage test through separate opening</p> <p>Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm</p> <p>Tool-free changeover of the cable outlet</p> <p>Park position for simpler maintenance work</p> <p>All variants also available with electronic fuse monitoring</p> |
| Material | <p>Polyamide (PA 6)</p> <p>Fire protection corresponding to UL 94</p> <p>Contact tracks: Electrolytic copper, silver-plated</p> |
| Colour | <p>RAL 9005</p> <p>RAL 35745</p> |
| Supply includes | Connectors for electronic fuse monitoring |
| For bar systems with centre-to-centre spacing | 60 mm |
| Cable outlet | Top/bottom |
| Type of electrical connection | Screw M8 |

Features

| | |
|--------------------------------------|--|
| Rated current max. | 160 A |
| Rated operating current max. | 160 A |
| Rated operating voltage | 690 V AC |
| For NH size | 00 |
| Test specification | IEC/DIN EN 60 947-3 DIN EN 60 269-2 (fuse inserts) |
| Dimensions | Width: 106 mm Height: 229.5 mm Depth: 104.5 mm |
| Operating temperature range | -5 °C...35 °C |
| Storage temperature range | -25 °C...70 °C |
| To fit busbars | 15 x 5/10 20 x 5/10 30 x 5/10 |
| To fit busbar system | RiLineX RiLine60 |
| Number of poles | 3-pole |
| Utilisation category | AC-23B (400 V/100 A) AC-22B (500 V/100 A) DC-22B (250 V/100 A) |
| Contamination level | 3 |
| with electronic fuse monitoring | Yes |
| IP protection category to IEC 60 529 | IP 2XB |
| Fire load | 16,6 MJ/m ² |
| Power dissipation (max.) | 19 W |
| Packs of | 1 pc(s). |
| Net weight | 1.135 |
| Gross weight | 1.155 |
| Copper weight (kg per piece) | 0.363 |

Features

Customs tariff number 85369095

ETIM 9 EC001040

Approvals

Explanations Declaration of conformity