

Rittal – The System.

Faster – better – everywhere.



RX 9362.110

RiLineX NH fuse-switch disconnector

State: 13.02.2026. (Source: ittal.com/hr-hr)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

RX 9362.110 - RiLineX NH fuse-switch disconnector

RiLineX NH fuse-switch disconnector in size 1 for 60 mm busbar systems. The cover can be locked and prepared for a lead seal. It also has visual fuse monitoring. Integrated measuring points on the cover ensure safe voltage testing. NH fuse-switch disconnectors have a park position to make maintenance easier. Size M10 screw terminal connection. Cable outlet can be at the top or bottom, as required.



Features

Model No.	RX 9362.110
Design	For 60 mm busbar systems
Benefits	<p>Cover: can be locked and prepared for a lead seal</p> <p>Voltage test through separate opening</p> <p>Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm</p> <p>Tool-free changeover of the cable outlet</p> <p>Park position for simpler maintenance work</p> <p>All variants also available with electronic fuse monitoring</p>
Material	<p>Polyamide (PA 6)</p> <p>Fire protection corresponding to UL 94</p> <p>Contact tracks: Electrolytic copper, silver-plated</p>
Colour	<p>RAL 9005</p> <p>RAL 35745</p>
For bar systems with centre-to-centre spacing	60 mm
Cable outlet	Top/bottom

Features

Type of electrical connection	Screw M10
Rated current max.	250 A
Rated operating current max.	250 A
Rated operating voltage	690 V AC
For NH size	1
Test specification	IEC/DIN EN 60 947-3 DIN EN 60 269-2 (fuse inserts)
Dimensions	Width: 181.5 mm Height: 298 mm Depth: 116.7 mm
Operating temperature range	-5 °C...35 °C
Storage temperature range	-25 °C...70 °C
To fit busbars	15 x 5/10 20 x 5/10 30 x 5/10
To fit busbar system	RiLineX RiLine60
Number of poles	3-pole
Utilisation category	AC-23B (400 V/100 A) AC-22B (500 V/100 A) DC-22B (250 V/100 A) DC-21B (440 V/100 A)
Contamination level	3
IP protection category to IEC 60 529	IP 2XB
Fire load	36,19 MJ/m ²
Power dissipation (max.)	51 W
Packs of	1 pc(s).
Net weight	2.273
Gross weight	2.448

Features

Copper weight (kg per piece)	0.8
Customs tariff number	85369095
ETIM 9	EC001040

Approvals

Explanations	Declaration of conformity
--------------	---------------------------