


# Rittal – The System.

Faster – better – everywhere.



## PK 9508.100

# Polycarbonate enclosures PK

State: 04.11.2025. (Source: [rittal.com/hr-hr](https://www.rittal.com/hr-hr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# PK 9508.100 - Polycarbonate enclosures PK without knockouts

Wall-mounted enclosure of fibreglass-reinforced polycarbonate. Protection category IP 66. Covers feature quick-release fasteners for speedy maintenance. Self-extinguishing material for safety.



## Features

|                                   |                                                                                                                                                                              |
|-----------------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Model No.                         | PK 9508.100                                                                                                                                                                  |
| Design                            | PK enclosure with transparent cover                                                                                                                                          |
| Product description               | Use within the ambient temperature range: -35 °C...+80 °C. The specified temperatures may be limited by the installed equipment.                                             |
| Material                          | Enclosure: Fibreglass-reinforced polycarbonate<br>Cover transparent: Polycarbonate, all-round foamed-in PU seal<br>Cover screws: Polyamide<br>Insulating bungs: Polyethylene |
| Colour                            | RAL 7035                                                                                                                                                                     |
| Supply includes                   | Enclosure with cover<br>Cover screws<br>Insulating bungs for wall mounting screws                                                                                            |
| Protection category NEMA          | NEMA 4X                                                                                                                                                                      |
| Protection category to IEC 60 529 | IP 66                                                                                                                                                                        |
| IK Code                           | IK08                                                                                                                                                                         |

# Features

|                             |                                                |
|-----------------------------|------------------------------------------------|
| Dimensions                  | Width: 130 mm<br>Height: 94 mm<br>Depth: 57 mm |
| Operating temperature range | -35 °C...80 °C                                 |
| Basic material              | Polycarbonate                                  |
| Packs of                    | 4 pc(s).                                       |
| Net weight                  | 0.772                                          |
| Gross weight                | 0.878                                          |
| Customs tariff number       | 94037000                                       |
| EAN                         | 4028177139275                                  |
| ETIM 9                      | EC000261                                       |
| ECLASS 8.0                  | 27180101                                       |

# Approvals

|           |            |
|-----------|------------|
| Approvals | C-UL<br>UL |
|-----------|------------|