

Rittal – The System.

Faster – better – everywhere.



SV 9635.110

Circuit-breaker component adaptor

State: 02.06.2026. (Source: rittal.com/hr-hr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9635.110 - Circuit-breaker component adaptor 3-pole

For mechanical attachment and direct contacting of circuit-breakers on the board.

Features

Model No.	SV 9635.110
Function principle	For mechanical attachment and direct contacting of circuit-breakers on the board Circuit-breaker is fitted using variably adjustable fixing points (M4)
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	RAL 7035
Note	Consider the mounting distance of the circuit-breaker when selecting the circuit-breaker component adaptor Depending on the circuit-breaker used, there may be a reduction in output The technical data may vary for UL applications
Rated current max.	160 A
Rated operating voltage	600 V (DC), 3~ 690 V (AC), 3~
Number of poles	3-pole
Dimensions	Width: 90 mm Height: 160 mm Depth: 45 mm
Distance between fixing points	30 mm
Cable outlet	Top/bottom
To fit manufacturer (model)	ABB (XT2) Allen Bradley (140G-H) Eaton (NZM1)
Packs of	1 pc(s).
Net weight	0,55 kg
Gross weight	0,588 kg

Features

Copper weight (kg per piece)	0,276
Customs tariff number	85369095
ETIM 9	EC001531
ECLASS 8.0	27370304
Product description	SV CB component adaptor 160 A, 690 V (AC), 600 V (DC), 3-pole WH: 90 x 160 mm, mounting distance 30 mm

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK
