


Rittal – The System.

Faster – better – everywhere.



SV 9635.400

Motor controller

State: 22.01.2026. (Source: rittal.com/hr-hr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9635.400 - Motor controller 3-pole

For controlling motors as direct or reversing starters with integral over-ride protection

Features

Model No.	SV 9635.400
Function principle	<p>For controlling motors as direct or reversing starters with integral over-ride protection</p> <p>The hybrid technology used facilitates frequent switching by semiconductors with zero wear</p> <p>During operation, mechanical contacts ensure a low heat loss</p> <p>Space-saving configuration thanks to the minimal build width</p>
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	RAL 7035
Power dissipation (max.)	2,8 W
Rated operating voltage	500 V (AC), 3~, 50 Hz/60 Hz
Rated current max.	0,6 A
Note	The technical data may vary for UL applications
Dimensions	Width: 22.5 mm Height: 160 mm Depth: 114 mm
Connection of round conductors	0.14 - 2.5 mm ²
Adjustable current monitoring	0.075 - 0.6 A
Packs of	1 pc(s).
Net weight	0.38
Gross weight	0.389
Customs tariff number	85371091
EAN	4028177817319
ETIM 9	EC002572

Features

ECLASS 8.0

27370804

Approvals

Approvals UL + C-UL (listed)

Explanations Declaration of conformity