

Rittal – The System.

Faster – better – everywhere.



AX 1350.450

AX kompakt kapcsolószekrény

Állapot: 2025.05.22. (Forrás: rittal.com/hu-hu)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AX 1350.450 - AX kompakt kapcsolószekrény C4-H

The compact enclosure AX with integral enclosure locators in the roof, base and side forms the familiar 25 mm system pitch pattern from the VX25 large enclosure. System components and accessories are easily, quickly and securely installed and retrofitted on rails, with no drilling required. Surface coating to DIN EN ISO 12944 corrosion protection class C4-H. Important: Please observe the product properties and the notes on installation and maintenance in the product description.

Jellemzők

Cikkszám	AX 1350.450
Kivitel	Surface coating to DIN EN ISO 12944
Előnyei	Több belső kiépítési lehetőség a 25 mm-es rendszerű raszterbe épített pozícionálóbütykök révén, belső kiépítésre szolgáló sínrel és sokoldalú rendszertartozékainkkal együtt Megtartja a védettséget (UL jóváhagyás), mivel a sínek a belső kiépítéshez fúrás nélkül felszerelhetők Kiegészítő szerelősík és megnövelt teherbírás a fenékképző sín révén Egyszerű tervezés és konfigurálás a Rittal RiPanel konfigurátorral
Anyag	Ház és ajtó: acéllemez Ajtó: acéllemez, körbefutó habosított poliuretán tömítés
Felület	Enclosure and door: Powder-coated, textured paint Szerelőlap: horganyzott
Szín	RAL 7035
Egységcsomag	Ház ajtóval/ajtókkal Bevezetőlemez a házfenékben Szerelőlap Lyuksoros szerelősín ajtóra Zár: kéttollú, 3 mm-es

Jellemzők

Megjegyzés	Installation and maintenance: DIN EN ISO 12944 refers to corrosion protection for steel structures (e.g. containers and bridges) and is thus only indirectly applicable to enclosures. The test criteria defined in this standard were nevertheless applied to the paint finishes of the C4-H enclosures. Our "paint finish equivalent to C4-H" thus satisfies all requirements of the standard in respect of the 720-hour salt spray mist test. Even so, corrosion can still occur on such sheet-steel enclosures. If the enclosure is installed in an environment where there is a risk of corrosion, the user must provide for regular maintenance and the prompt repairing of any paint damage. Depending on the application, the user may need to take suitable precautions as protection against environmental conditions at the place of installation, e.g. UV radiation.
NEMA védettség	NEMA 1, 3R, 4, 12
IP védettség EN 60 529 szerint	IP 66
IK-kód	IK10
Méret	Szélesség: 500 mm Magasság: 500 mm Mélység: 300 mm
Szerelőlap anyagvastagsága	2,5 mm
Szerelőlap mérete (Szé x Ma)	450 mm x 475 mm
Ajtók száma	1
Cserélhető ajtópánt	Igen
Zár	Zár kivitel: Elforduló zár Zárak száma: 2 Zárbetét: Kéttollú, 3 mm
Kábelbevezető lemez	Méret: 6 Mennyiség: 1
Alapanyag	Acéllemez
Csomagolási egység	1 db
PCF per pack (cradle-to-gate)	74,4 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared

Jellemzők

EAN	4028177993785
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101