



Rittal – The System.

Faster – better – everywhere.



VX 1182.097

VX IT Open

State: 6/08/2025 (Source: [rittal.com/ie-en](https://www.rittal.com/ie-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 1182.097 - VX IT Open

VX IT standard version, without front and rear door. Usable either as an open 482.6 mm (19") frame in a secure environment or as the basis for fast configurations in the Rittal RiPanel configuration system using existing accessories (such as doors and side panels) from the Rittal modular range.



Features

| | |
|----------------|--|
| Model No. | VX 1182.097 |
| Design | VX enclosure frame with roof plate without front and rear door Vented without side panels |
| Surface finish | Enclosure frame: Dipcoat-primed Interior installation: Spray-finished |
| General colour | RAL 7035 |
| Colour | Enclosure frame and roof: RAL 7035 Interior installation: RAL 9005 |

Features

| | |
|---|---|
| Supply includes | <p>Enclosure frame</p> <p>Mounting angles, 482.6 mm (19")</p> <p>Spacers, height 50 mm, to raise a cover plate above the fan cut-out in the roof plate, for passive cooling (supplied loose). Not required for variants without a cut-out.</p> <p>12 x 482.6 mm (19") fastener, 1 U, conductive (supplied loose)</p> <p>25 multi-tooth screws, conductive (supplied loose)</p> <p>IPPC pallet</p> <p>Roof plate, multi-piece, with side cable entry in the depth, double-sided, prepared for fan mounting plate</p> |
| Dimensions | <p>Width: 800 mm</p> <p>Height: 2,000 mm</p> <p>Depth: 1,200 mm</p> |
| Units | 42 U |
| Free mounting space to the 482.6 mm (19") level, front/rear | 150 mm / 330 mm |
| Distance between levels as delivered | 720 mm |
| 482.6 mm (19") attachment | screw-fastened onto depth stays, top and bottom, and to the support rail on the frame structure |
| Design | Standard |
| Roof design | multi-piece, with side cable entry in the depth, double-sided, prepared for fan mounting plate |
| Mounting angle design | 482.6 mm (19") mounting angles, standard in the VX IT |
| Base design | Open |
| 482.6 mm (19") level(s) version | front and rear |
| Load capacity | 15,000 N |
| Max. load capacity (static) per enclosure to UL 2416 | 12,000 N |
| Basic material | Sheet steel |
| Packs of | 1 pc(s). |
| Net weight | 73 |

Features

| | |
|--------------|---------------|
| Gross weight | 76 |
| EAN | 4028177973299 |
| ETIM 9 | EC002499 |
| ETIM 8 | EC002499 |
| ECLASS 8.0 | 27180207 |

Approvals

| | |
|--------------|---|
| Explanations | Manufacturer's declaration Declaration of conformity |
|--------------|---|