


Rittal – The System.

Faster – better – everywhere.



KX 1541.000

Terminal box KX, sheet steel, with gland plate

State: 1/02/2026 (Source: rittal.com/ie-en)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

KX 1541.000 - Terminal box KX, sheet steel, with gland plate

The small enclosure KX, terminal box KX, with a gland plate allows for flexible interior installation and simple cable entry with optimum use of space.



Features

| | |
|-----------------------------------|--|
| Model No. | KX 1541.000 |
| Material | Enclosure: Sheet steel Cover: Sheet steel, all-round foamed-in PU seal |
| Surface finish | Enclosure and cover: Dipcoat primed, powder-coated on the outside, textured paint |
| Colour | RAL 7035 |
| Supply includes | Enclosure with cover Mini cam locks Sheet steel gland plates with seals and assembly parts |
| Protection category NEMA | NEMA 1 NEMA 12 |
| Protection category to IEC 60 529 | IP 55 |
| Type rating to UL 50E | Type 1 Type 12 |
| IK Code | IK08 |

Features

| | |
|--------------------------------|--|
| Dimensions | Width: 800 mm Height: 400 mm Depth: 120 mm |
| Material thickness - cover | 1.25 mm |
| Material thickness - enclosure | 1.25 mm |
| Gland plates | : 1 + 1 : 3 + 3 |
| Basic material | Sheet steel |
| Packs of | 1 pc(s). |
| Net weight | 10.541 |
| Gross weight | 11.65 |
| PCF per pack (cradle-to-gate) | 44.6 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 84879059 |
| EAN | 4028177816466 |
| E-Number Sweden | E3465212 |
| ETIM 9 | EC000261 |
| ETIM 8 | EC000261 |
| ECLASS 8.0 | 27180101 |

Approvals

| | |
|--------------|---|
| Approvals | Bureau Veritas DNV-GL Lloyds Register of Shipping UL + C-UL (listed) |
| Certificates | Protection category |

Approvals

Explanations

Declaration of conformity
Declaration of conformity UK
PCF-declaration