

Rittal – The System.

Faster – better – everywhere.



SR 2342.235

Swing frame, large, with trim panel

State: 23/05/2026 (Source: rittal.com/ie-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SR 2342.235 - Swing frame, large, with trim panel for TS, VX SE 800 mm wide enclosures

For 800 mm wide enclosures, 22 - 45 U, with trim panel, for mounting 482.6 mm (19") equipment.



Features

| | |
|----------------------|--|
| Model No. | SR 2342.235 |
| Design | 482.6 mm (19") level, centre |
| Product description | For mounting 482.6 mm (19") equipment. |
| Material | Sheet steel |
| Surface finish | Frame: Zinc-plated Trim panel: Spray-finished |
| Colour | RAL 7035 |
| Supply includes | Locking rod system with double-bit lock insert Material for attaching |
| Installation options | In the TS/SE with 180° opening angle |
| Assembly instruction | Depending on the mounting situation, TS punched sections with mounting flanges 23 x 73 mm or 17 x 73 mm are required |

Features

| | |
|-----------------------|--|
| Note | For further installation options, see "Technical details" For two-door enclosures TS, SE with a height of 1800 or 2200 mm the next-smallest swing frame must be installed, due to collision with the lock |
| To fit | Enclosure type: TS VX SE Width: = 800 mm Height: ≥ 2,000 mm |
| Units | 40 U |
| To fit enclosure type | TS VX SE |
| Packs of | 1 pc(s). |
| Net weight | 19 kg |
| Gross weight | 21.5 kg |
| Customs tariff number | 94039910 |
| ETIM 9 | EC002620 |
| ETIM 8 | EC002620 |
| ECLASS 8.0 | 27189261 |
| Product description | SR Swing frame, large, with trim panel, for TS, VX SE, for W: 800 mm, 40 U, installed at the centre |

Tender text

Large swing frame for network enclosure

40 U can be used for accommodating 482.6 mm (19") equipment.

Torsionally stiff frame, welded from rectangular tube and triple folded support section. Load capacity up to 1500 N when standard hinges are used. Distance from inside edge of door to front edge of swing frame 100 mm, may be installed deeper on a pitch pattern of 25 mm. The swing frame must be fitted to the left / to the right depending on the installation depth of the equipment.

Installation position of equipment mounted in the centre.

Material: sheet steel

Surface finish: RAL 7035

for enclosure width: W: 800 mm