

Rittal – The System.

Faster – better – everywhere.



SG 2372.102

Signal pillar 3-way LED

State: 18/04/2026 (Source: rittal.com/ie-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SG 2372.102 - Signal pillar 3-way LED

Identify malfunctions and operating statuses in machines and automated processes immediately with Rittal's flexible range of signal pillars to suit all applications. If you only need three standard signal colours, the plug-and-play 3-way LED signal system is the ideal choice.

Features

| | |
|-----------------------------------|--|
| Model No. | SG 2372.102 |
| Design | for wall/base mounting |
| Benefits | Complete, ready-to-connect solution Extremely long service life of the LEDs (max. 100,000 hours, therefore maintenance-free) Minimal assembly work and warehousing costs |
| Technical specifications | 3-stage, red, yellow, green Transmission angle: 3 x 120° |
| Cable entry | Min. cable diameter: 3 mm Max. cable diameter: 6.5 mm |
| Type of electrical connection | Screwless spring terminals |
| Light | LEDs |
| Dimensions | Height: 211.5 mm |
| Operating temperature range | -20 °C...50 °C |
| Protection category to IEC 60 529 | IP 65 |
| Rated operating voltage | 24 V |
| Thread | M12 x 1.5 |
| Note | The signal pillar is comprised of items 2372001, 2372021, 2372011 and 2368002 |
| Packs of | 1 pc(s). |
| Net weight | 0.25 kg |
| Gross weight | 0.309 kg |
| Customs tariff number | 85318070 |

Features

| | |
|---------------------|---|
| ETIM 9 | EC001042 |
| ETIM 8 | EC001042 |
| ECLASS 8.0 | 27371230 |
| Product description | SG signal pillar, LED compact for wall mounting |

Approvals

| | |
|-----------|--------------------|
| Approvals | UL + C-UL (listed) |
|-----------|--------------------|
