

Rittal – The System.

Faster – better – everywhere.



SZ 2411.671

Cable gland, polyamide

State: 11/05/2026 (Source: rittal.com/ie-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2411.671 - Cable gland, polyamide

Integrated clamping membranes ensure reliable tightening and strain relief to protect the cables.

Features

| | |
|-------------------------------------|--|
| Model No. | SZ 2411.671 |
| Benefits | Because the gland and lock nut are sold together in a single pack, this saves additional ordering and storage. Clamping membranes for even tightening and strain relief to protect the cables |
| Material | Polyamide 6 Seal: CR/NBR |
| Colour | RAL 7035 |
| IP protection category to IEC 60529 | IP 68 (5 bar, 30 min) |
| Dimensions | Height: 53 mm |
| Thread | M63 x 1.5 |
| Thread length | 18 mm |
| Min. cable diameter | 34 mm |
| Max. cable diameter | 44 mm |
| Operating temperature range | -30 °C...100 °C |
| torque | 25 Nm |
| Width across flats | 65 mm |
| Dimensions | Thread: M63 x 1.5 Thread length: 18 mm |
| Type rating to UL 50E | Type 1 Type 4 Type 4X Type 12 Type 13 |
| Packs of | 3 pc(s). |

Features

| | |
|-----------------------|---|
| Net weight | 0.372 kg |
| Gross weight | 0.375 kg |
| Customs tariff number | 39269097 |
| ETIM 9 | EC000441 |
| ETIM 8 | EC000441 |
| ECLASS 8.0 | 27149109 |
| Product description | SZ Cable gland, polyamide, size: M63x1,5, for cables ø 34-44 mm |

Approvals

| | |
|--------------|---|
| Approvals | CSA + CSAus UL + C-UL (listed) VDE |
| Explanations | Declaration of conformity Declaration of conformity UK |
