

Rittal – The System.

Faster – better – everywhere.



SZ 2411.801

Cable gland, brass

State: 24/08/2025 (Source: [rittal.com/ie-en](https://www.rittal.com/ie-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2411.801 - Cable gland, brass

Integrated clamping membrane ensure safe tightening and cable-friendly strain relief.

Features

| | |
|-------------------------------------|--|
| Model No. | SZ 2411.801 |
| Benefits | Because the gland and lock nut are sold together in a single pack, this saves additional ordering and storage. Clamping membranes for even tightening and strain relief to protect the cables |
| Material | Brass Seal: CR/NBR |
| Surface finish | Nickel-plated |
| IP protection category to IEC 60529 | IP 68 (5 bar, 30 min) |
| Dimensions | Height: 22 mm |
| Thread | M12 x 1.5 |
| Thread length | 6 mm |
| Min. cable diameter | 3 mm |
| Max. cable diameter | 6.5 mm |
| Operating temperature range | -40 °C...100 °C |
| torque | 5.5 Nm |
| Width across flats | 14 mm |
| Dimensions | Thread: M12 x 1.5 Thread length: 6 mm |
| Type rating to UL 50E | Type 4X |
| Packs of | 15 pc(s). |
| Net weight | 0.195 |
| Gross weight | 0.222 |

Features

| | |
|-----------------------|---------------|
| Customs tariff number | 74198090 |
| EAN | 4028177809994 |
| ETIM 9 | EC000441 |
| ETIM 8 | EC000441 |
| ECLASS 8.0 | 27149109 |

Approvals

| | |
|--------------|---|
| Approvals | UR + C-UR (recognized) VDE |
| Explanations | Declaration of conformity Declaration of conformity UK |