

# Rittal – The System.

Faster – better – everywhere.



## SZ 2482.210

# Interface extension with wall connection

State: 23/06/2025 (Source: [rittal.com/ie-en](http://rittal.com/ie-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2482.210 - Interface extension with wall connection

For extending the internal enclosure interfaces – e.g. from industrial PCs and switches – up to the outside of the enclosure.

## Features

|                                      |   |
|--------------------------------------|---|
| Model No.                            | SZ 2482.210   |
| Design                               | USB 2.0 wall-mounted jack type A on internal connector type A   |
| Product description                  | For extending the internal enclosure interfaces – e.g. from industrial PCs and switches – up to the outside of the enclosure. The wall connection only needs the same space as a switch.                                |
| Benefits                             | Rapid access for maintenance work<br>The protection category of the enclosure is preserved<br>The lock nut cuts automatically into the spray-finish, thereby creating a conductive connection<br>Captive protective cap |
| Material                             | Enclosure: Brass<br>Cover: Aluminium<br>Seal: Polyamide   |
| Surface finish                       | Enclosure: Nickel-plated<br>Cover: Natural anodised   |
| Length                               | 0.5 m   |
| Dimensions                           | Length: 0.5 m   |
| For wall thickness (max.)            | 1 - 6 mm  |
| IP protection category to IEC 60 529 | IP67 with sealed protective cap   |
| Packs of                             | 1 pc(s).  |
| Net weight                           | 0.08  |
| Gross weight                         | 0.087   |
| Customs tariff number                | 85369095  |
| EAN                                  | 4028177516311   |

# Features

|            |          |
|------------|----------|
| ETIM 9     | EC001408 |
| ETIM 8     | EC001408 |
| ECLASS 8.0 | 19059205 |