## Rittal – The System.

Faster - better - everywhere.





# SZ 2500.320 LED system light

State: 27/10/2025 (Source: rittal.com/ie-en)



## SZ 2500.320 - LED system light

LED system light – the first light especially for enclosures! Highly innovative LED technology for even more light into the very last corner.





#### **Features**

Model No.	SZ 2500.320
Design	With motion detector
Benefits	Optimum illumination of the entire enclosure Optionally with clip, screw and magnetic attachment
	A configuration to suit every application
Design	Motion sensor
	90° rotating connector
	Adjustable light direction
	Adjustable light distribution
Material	Light body: Extruded aluminium
	Light cover: Polycarbonate
	Light ends: PC-ABS
Colour	Enclosure: RAL 7016
Supply includes	Assembly screws
Power consumption	13 W
Connection options	Infeed, 2-pole
	Through-wiring, 2-pole
Motion detector	Yes

© Rittal 2025

## Features

Protection class	III (SELV)
Light – installation type	Screw-fastening Clip attachment Magnetic attachment (accessory)
Installation options	Directly onto the enclosure section with 25 mm pitch pattern
Luminous flux	1,200 lm
Light colour	4000 K (neutral white)
Note	Connection accessories should be ordered separately
Dimensions	Width: 437 mm Height: 85 mm Depth: 37 mm
Operating temperature range	-20 °C55 °C
Rated operating voltage	24 V - 56 V (DC)
IP protection category to IEC 60 529	IP 20
Packs of	1 pc(s).
Net weight	0.488
Gross weight	0.65
Customs tariff number	94054990
EAN	4028177918818
ETIM 9	EC000321
ETIM 8	EC000321
ECLASS 8.0	27189241

# Approvals

Approvals	cqc-ccc
	UL + C-UL (listed)

© Rittal 2025 3

## **Approvals**

Explanations

Declaration of conformity

Declaration of conformity UK

© Rittal 2025